





P.C.B LAYOUT

<i>PIN</i>	$\phi 1.0$	$\phi 1.3$
<i>APPD.</i>		

					TOLERANCE UNLESS SPECIFIED									
6	DC-045 PING	BRASS	1	Ni PLATED	UP TO 5mm:±0.1	ANGULAR	1							
5	DC-092 4#COVER	SUS	1	Ag PLATED	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
4	DC-045 2#SPRING	SUS	1	Ag PLATED	TITLE:DC JACK			UNIT : MM	ROHS	DWN				
3	DC-045 1#FLAT PIECE	BRASS	1	Ag PLATED	MODEL:			SCALE: 6:1	COMPLIANT	CHK'D				
2	DC-045 3#CURVE PIECE	BRASS	1	Ag PLATED	东莞市六钧电子五金有限公司							APPD		
1	DC-045 CASE	PA9T	1	BLACK										
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO.AGL:		REV : A