







P.C.B LAYOUT
TOP VIEW



H=1.7mm

SCHEMATIC



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50\text{gf}$
- 6.Travel: $0.15\pm 0.1\text{mm}$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 9.Sign "*" is importance dimension.

					TOLERANCE UNLESS SPECIFIED									
6	STEM	BRASS	1		<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1	2024.4.9	⚠ 按实物增加材质PI膜/盖子无电镀			MLQ		
5	COVER	SUS	1	⚠			NO	DATE	REVISIONS			BY	APPD	
4	TAPE	PI ⚠	1	YELLOW	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN			
3	CONTACT	SUS	1	Ag-Plated	MODEL: TS-1187-017C-HTF			SCALE: 1:1		COMPLIANT	CHK'D			
2	TERMINAL	BRASS	4	Ag-Plated	东莞市六钧电子五金有限公司						APPD			
1	HOUSING	LCP	1	BLACK										
NO.	PART NAME	MATERIAL	QTY	FINISHING										
											PRO.AGL:	⚠	⊕	REV :A1