

### FEATURES

- High Accurate  $\pm 2\%$
- Precision monitoring of +3V, +3.3V, and +5V Power supply voltage
- Fully specified over temperature
- Available in three output configurations
- Push-Pull RESET low output (MAX809)
- Push-Pull (RESET) high output (MAX810)
- 200ms typ. Power-on reset pulse width
- 25 $\mu$ s supply current
- Guaranteed reset valid to  $V_{CC}=+1V$
- Power supply transient immunity

The MAX809/810 series are used for microprocessor ( $\mu$ P) supervisory circuits to monitor the power supplies in  $\mu$ P and digital systems. They provide excellent circuit reliability and low cost by eliminating external components and adjustments when used with +5V, +3.3V, +3.0V, +2.5V powered circuits.

These circuits perform a single function: they assert a reset signal whenever the  $V_{CC}$  supply voltage declines below a preset threshold, keeping it asserted for at least 200ms after  $V_{CC}$  has risen above the reset threshold. Reset thresholds suitable for operation with a variety of supply voltages are available. MAX809/810 series have push pull outputs. MAX809 series has an active low

### APPLICATION

- Battery-operated systems and controllers
- Intelligent instruments
- Critical  $\mu$ P and  $\mu$ C power monitoring
- Portable / Battery powered equipment
- Automotive

RESET output, while the MAX810 has an active high RESET output. The reset comparator is designed to ignore fast transients on  $V_{CC}$ , and the outputs are guaranteed to be in the correct logic state for  $V_{CC}$  down to 1.0V. Low supply current makes MAX809/810 series ideal for use in portable equipment.

### Ordering Information


MAX810R

RESET VOLTAGE: L=4.63V  
M=4.38V  
J=4.00V  
T=3.08V  
S=2.93V  
R=2.63V



### Marking:

MAX809L: AAAA  
MAX810L: AGAA  
MAX809M: ABAA  
MAX810M: AHAA  
MAX809J: CWAA  
MAX809T: ACAA  
MAX810T: AJAA  
MAX809S: ADAA  
MAX810S: AKAA  
MAX809R: AF AA  
MAX810R: ALAA

## TYPICAL APPLICATIN CIRCUIT



## Pin Definition



### ABSOLUTE MAXIMUM RATINGS

| PARAMETER                              | SYMBOL      | LIMIT                       | UNIT |
|--|-------------|-----------------------------|------|
| Terminal Voltage (with respect to GND) | $V_{CC}$    | GND - 0.3 to GND +6.5       | V    |
| <u>RESET</u> & (RESET) push-pull       | $V_{RESET}$ | GND - 0.3 to $V_{CC}$ +0.3  | V    |
| Input Current, $V_{CC}$                | $I_{CC}$    | 20                          | mA   |
| Output Current, <u>RESET</u> , (RESET) | $I_O$       | 5                           | mA   |
| Power Dissipation                      | $P_D$       | $(T_J - T_A)/R_{\theta JA}$ | mW   |
| Operating Junction Temperature Range   | $T_{J,OPR}$ | -40 ~ +125                  | °C   |
| Storage Temperature Range              | $T_{STG}$   | -65 ~ +150                  | °C   |
| Lead Soldering Temperature (260°C)     | $T_{LEAD}$  | 10                          | s    |

### THERMAL PERFORMANCE

| PARAMETER   | SYMBOL          | MAXIMUM | UNIT |
|---|-----------------|---------|------|
| Thermal Resistance from Junction to Case                        | $R_{\theta JC}$ | 110     | °C/W |
| Thermal Resistance from Junction to Ambient <sup>(Note 1)</sup> | $R_{\theta JA}$ | 250     | °C/W |

### ELECTRICAL CHARACTERISTICS ( $V_{CC} = 5V$ , $T_A = 25^\circ C$ unless otherwise noted)

| PARAMETER                               | CONDITIONS  | SYMBOL      | MIN          | TYP  | MAX  | UNIT            |
|---|---|-------------|--------------|------|------|-----------------|
| Input Supply Voltage                    | $T_A = -40^\circ C \sim +85^\circ C$                  | $V_{CC}$    | 1.0          | --   | 6    | V               |
| Supply Current                          | $V_{CC} = V_{TH} + 1V$                                | $I_{CC}$    | --           | 25   | 35   | $\mu A$         |
| Reset Threshold                         | MAX809/810L   | $V_{TH}$    | 4.54         | 4.63 | 4.71 | V               |
|   | MAX809/810M   |             | 4.29         | 4.38 | 4.46 |                 |
|   | MAX809/810J   |             | 3.92         | 4.00 | 4.08 |                 |
|   | MAX809/810T   |             | 3.02         | 3.08 | 3.15 |                 |
|   | MAX809/810S   |             | 2.87         | 2.93 | 3.00 |                 |
|   | MAX809/810R   |             | 2.57         | 2.63 | 2.69 |                 |
| Reset Threshold Temperature Coefficient | $T_A = 0 \sim +85^\circ C$                            | $V_{THT}$   | --           | 50   | --   | ppm/ $^\circ C$ |
| Set-up Time                             | $V_{CC} = 0 \sim (V_{TH} - 100mV)$                    | $T_{SET}$   | 1            | --   | --   | $\mu s$         |
| $V_{CC}$ to Reset Delay                 | $V_{CC} = V_{TH} \sim (V_{TH} - 100mV)$               | $T_{RD}$    | --           | 20   | --   | $\mu s$         |
| Reset Active Timeout Period             | $T_A = 0 \sim +85^\circ C$                            | $T_{DELAY}$ | 140          | 200  | 260  | ms              |
| RESET Output (MAX809) Voltage Low       | $1.8V < V_{CC} < V_{TH(MAX)}$ ,<br>$I_{SINK} = 1.2mA$ | $V_{OL}$    | --           | --   | 0.3  | V               |
|   | $1.2V < V_{CC} < 1.8V$ ,<br>$I_{SINK} = 50\mu A$      |             |              |      |      |                 |
| RESET Output (MAX809) Voltage High      | $V_{CC} > V_{TH(MAX)}$ ,<br>$I_{SOURCE} = 500\mu A$   | $V_{OH}$    | $0.8 V_{CC}$ | --   | --   | V               |
| (RESET) Output (MAX810) Voltage Low     | $V_{CC} > V_{TH(MAX)}$ , $I_{SINK} = 1.2mA$           | $V_{OL}$    | --           | --   | 0.3  | V               |


### ELECTRICAL CHARACTERISTICS ( $V_{CC} = 5V$ , $T_A = 25^\circ C$ unless otherwise noted)

| PARAMETER                            | CONDITIONS   | SYMBOL    | MIN          | TYP | MAX | UNIT |
|--------------------------------------|--|-----------|--------------|-----|-----|------|
| (RESET) Output (MAX810) Voltage High | $1.8V < V_{CC} < V_{TH(MAX)}$ ,<br>$I_{SOURCE} = 500\mu A$ | $V_{OH}$  | $0.8 V_{CC}$ | --  | --  | V    |
|                                      | $1.2V < V_{CC} < 1.8V$ ,<br>$I_{SOURCE} = 150\mu A$        |           |              |     |     |      |
| Hysteresis at $V_{CC}$               | Input Voltage  | $V_{HVS}$ | --           | 40  | --  | mV   |

**Note :**

1.  $R_{\theta JA}$  is measured the PCB copper area of approximately  $1in^2$  (Multi-layer). Needs to connect to  $V_{SS}$  pin.

**BLOCK DIAGRAM**



## APPLICATION INFORMATION

Negative-Going  $V_{CC}$  transients in addition to issuing a reset to the  $\mu P$  during power-up, power-down, and brownout conditions, the MAX809/810 are relatively immune to short-duration negative-going  $V_{CC}$  transients (glitches).

The MAX809/810 does not generate a reset pulse. The graph was generated using a negative going pulse applied to  $V_{CC}$ , starting 0.5V above the actual reset threshold and ending below it by the magnitude indicated (reset comparator overdrive). The graph indicates the maximum pulse width a negative going  $V_{CC}$  transient can have without causing a reset pulse. As the magnitude of the transient increases (goes farther below the reset threshold), the maximum allowable pulse width decreases. Typically, a  $V_{CC}$  transient that goes 100mV below the reset threshold and lasts 20 $\mu$ S or less will not cause a reset pulse. A 0.1 $\mu$ F bypass capacitor mounted as close as possible to the  $V_{CC}$  pin provides additional transient immunity.

## FUNCTION DESCRIPTION

A microprocessor's reset input starts the  $\mu P$  in a known state. The MAX809/810 assert reset to prevent code-execution errors during power-up, power-down, or brownout conditions. They assert a reset signal whenever the  $V_{CC}$  supply voltage declines below a preset threshold, keeping it asserted for at least 140ms after  $V_{CC}$  has risen above the reset threshold. The MAX809/810 have a push-pull output stage.


## ENSURING A VALID RESET OUTPUT DOWN TO $V_{CC}=0$

RESET is guaranteed to be a logic low for  $V_{CC} > 1.0V$ . Once  $V_{CC}$  exceeds the reset threshold, an internal timer keeps RESET low for the reset timeout period; after this interval, RESET goes high. If a brownout condition occurs ( $V_{CC}$  dips below the reset threshold), RESET goes low. Any time  $V_{CC}$  goes below the reset threshold, the internal timer resets to zero, and RESET goes low. The internal timer starts after  $V_{CC}$  returns above the reset threshold, and RESET remains low for the reset timeout period. When  $V_{CC}$  falls below 1V, the MAX809/810 reset output no longer sinks current - it becomes an open circuit. Therefore, high impedance CMOS logic input connected to reset can drift to undetermined voltages. This presents no problem in most applications since most  $\mu P$  and other circuitry is inoperative with  $V_{CC}$  below 1V. However, in applications where reset must be valid down to 0V, adding a pull down resistor to reset causes stray leakage currents to flow to ground, holding reset low (Figure 2.) R1's value is not critical; 100K is large enough not to load reset and small enough to pull RESET to ground. For the MAX809/810 if reset is required to remain valid for  $V_{CC} < 1V$ .

## BENEFITS OF HIGHLY ACCURATE RESET THRESHOLD

Most  $\mu P$  supervisor ICs have reset threshold voltages between 5% and 10% below the value of nominal supply voltages. This ensures a reset will not occur within 5% of the nominal supply, but will occur when the supply is 10% below nominal. When using ICs rated at only the nominal supply  $\pm 5\%$ , this leaves a zone of uncertainty where the supply is between 5% and 10% low, and where the reset may or may not be asserted.


## TIMING DIAGRAM





**Package information**

[www.sot23.com.tw](http://www.sot23.com.tw)



| Symbol | Dimensions In Millimeters |      |
|--------|---------------------------|------|
|        | Min                       | Max  |
| A1     | 0.02                      | 0.1  |
| A2     | 1.0Typical                |      |
| b      | 0.4Typical                |      |
| c      | 0.1Typical                |      |
| D      | 2.70                      | 3.10 |
| E      | 1.10                      | 1.50 |
| E1     | 2.20                      | 2.60 |
| e1     | 1.80                      | 2.00 |
| L      | 0.35                      | 0.48 |