



SPECIFICATION


1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
4. Withstanding voltage : 250VAC .
5. Operating Force: $250 \pm 50\text{gf}$
6. life test: 100,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

SCHEMATIC



H=3.1MM

P.C.B LAYOUT
TOP VIEW



					TOLERANCE UNLESS SPECIFIED											
					UP TO 5mm: ±0.1	ANGULAR	1	2017.4.17	更新图面							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS			BY	APPD			
5	CONTACT	PBS	1	Ag CLAD												
4	CONTACT FOOT	BRASS	2	Ag-Plated	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN					
3	COAT	SUS	1	Ag-Plated	MODEL: TS-1157A-031E				SCALE: 1:1	COMPLIANT	CHK'D					
2	BUTTON	PA6T	1		东莞市六钧电子五金有限公司								APPD			
1	HOUSING	PA6T	1													
NO.	PART NAME	MATERIAL	QTY	FINISHING												