






SCHEMATIC

P.C.B LAYOUT
TOP VIEW

H=1.5mm

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 300gf
- 6.Travel: $0.15\pm 0.1\text{mm}$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 9.Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED							
6	STEM	BRASS	1		<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1	2024.4.9	⚠ 按实物增加材质PI膜/盖子无电镀		MLQ	
5	COVER	SUS	1	⚠			NO	DATE	REVISIONS		BY APPD	
4	TAPE	PI ⚠	1	YELLOW	TITLE: TACT SWITCH			UNIT : MM		ROHS	DWN	
3	CONTACT	SUS	1	Ag-Plated	MODEL: TS-1187-015F PPA			SCALE: 1:1		COMPLIANT	CHK'D	
2	TERMINAL	BRASS	4	Ag-Plated	东莞市六钧电子五金有限公司					APPD		
1	HOUSING	PPA	1	BLACK								
NO.	PART NAME	MATERIAL	QTY	FINISHING						PRO.AGL:	 	REV :A1