



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

技术要求:

- 1) 材质:见附表;
- 2) 电镀:见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

适应基板厚度: 1.2mm~1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 3A




接触电阻: < 0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V AC/minute

TABLE:

CSG PART NO.	PIN#	Dimension mm	
		DIM A	DIM B
WAFER-XHB254WZ-2AH	2P	7.50	2.50
WAFER-XHB254WZ-3AH	3P	10.00	5.00
WAFER-XHB254WZ-4AH	4P	12.50	7.50
WAFER-XHB254WZ-5AH	5P	15.00	10.00
WAFER-XHB254WZ-6AH	6P	17.50	12.50
WAFER-XHB254WZ-7AH	7P	20.00	15.00
WAFER-XHB254WZ-8AH	8P	22.50	17.50
WAFER-XHB254WZ-9AH	9P	25.00	20.00
WAFER-XHB254WZ-10AH	10P	27.50	22.50
WAFER-XHB254WZ-11AH	11P	30.00	25.00
WAFER-XHB254WZ-12AH	12P	32.50	27.50
WAFER-XHB254WZ-15AH	15P	40.00	35.00



PCB LAYOUT

NO.	NAME	Q' TY	DESCRIPTION
2	PIN	n PCS	材质:黄铜,电镀:镀亮锡60u"MIN
1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:本色

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
 X :±0.35 X :±2°
 X.X :±0.25 X.X :±1°
 X.XX :±0.15



东莞市汉博电子科技有限公司
 DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	WAFER XHS 2.54立式DIP弯针红色			
DWN	xiong	PART NO.WAFER-XHB254WZ-NAH		
CHKD	lee	SCALE:1:1	UNIT: mm	☉
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY