


■ Description 产品描述:

Al-Ecap, 330uF, 6.3v, ±20%, Low ESR, D6.3H8.7mm, 5000Hrs@105℃, -55~+105℃, SMD.

■ Dimension& Marking 印刷及尺寸:




Items	A	B	C	D	P	L	α	W	H
Case Φ6.3x8.7	6.6	6.6	7.3	6.3	2.0	8.7	±0.3	0.5~0.8	0.5max.

■ Features 特长/用途:

- 105℃, Long life 宽温长寿命
- Low impedance capacitors 低阻抗
- Designed for surface mounting on high density PC board 适合高密度表面安装

■ Serie Expansion 系列拓展




Items 项目	Performance 性能			
Rated Voltage 额定电压(V _R)	6.3 V			
Capacitance 额定容量(C _R)	330 uF (120Hz, 20℃)			
Category Temperance Range 类别温度范围	-55℃ ~ +105℃			
Capacitance Tolerance 容量误差	-20% ~ +20% (120Hz, 20℃)			
Surge Voltage 浪涌电压(V _S)	7.25 V _{DC}			
Leakage Current 泄漏电流(I _{LC})	I _{LC} ≤ 20.79 uA After 2 minutes			
Dissipation Factor (Tanδ) 损失角正切值	≤ 0.26 (120Hz, 20℃)			
Impedance 阻抗 (Z, Ω)	≤ 0.6 (100kHz, 20℃)			
Ripple Current 纹波电流(I _{RC, rms})	230 mA (100kHz, 105℃)			
Low Temperature Characteristics 温度特性(120Hz)	Impedance ratio 阻抗比(Max.)	Z _(-25℃) / Z _(+20℃)	4	
		Z _(-55℃) / Z _(+20℃)	8	
Endurance and Shelf Life 耐久性及高温无负荷特性	Items 项目	Endurance 耐久性		Shelf Life Test 高温无负荷
	Test Time 测试时长	5,000 Hrs at 105℃; V _R		1,000 Hrs at 105℃
	Cap. Change 容量变化率	Within ±30% of initial Value ≤初始值的±30%		Within ±30% of initial Value ≤初始值的±30%
	Tanδ 损失角正切值	Less than 300% of specified Value ≤初始规格值的±300%		Less than 300% of specified Value ≤初始规格值的±300%
	Leakage Current 漏电流	Whitin specified Value ≤初始规格值		Whitin specified Value ≤初始规格值
Ripple Current and Frequency Multipliers 纹波电流频率系数	Frequency (Hz)	120	1k	10k
	Multiplier	0.65	0.85	0.95
Standards 参考标准	JIS C 5101-1, -18, IEC 60384-4			
Remarks 附注	RoHS Compliance, Halogen-free			

* Please refer to "Precautions and Guidelines for Aluminum Electrolytic Capacitors" section in catalog for further details 详细信息请参阅目录中的“铝电解电容器注意事项和指南”


Publication Date 发行日期	2022-02-15	Approved 批准 Checked 复核 Designed 设计	Lei Yang Chao Yu	
Revision Date 修订日期				
Version No.	1.0			

■ Taping Specifications 编带规格:



Case 尺寸	W (mm)	W1 (mm)	F (mm)	P (mm)	P1 (mm)	P2 (mm)	A (mm)	B (mm)	t1 (mm)	t2 (mm)
Tolerance 误差	±0.3	±0.15	±0.1	±0.1	±0.1	±0.1	±0.2	±0.2	±0.1	±0.2
Φ6.3x8.7	16	1.75	7.5	12	2	4	7	7	0.4	9.3


■ Park 包装:



Case 产品尺寸	Reel 卷装数量	Box 盒装数量	A±0.3(mm)	B±2(mm)	Box size 外箱尺寸(L*W*H)
Φ6.3x8.7	700	7000	18	382	395x235x395

■ Soldering Conditions 焊接条件:

1. The following conditions are recommended for air convection and infrared reflow soldering on the SMD products onto a glass epoxy circuit boards by cream solder. The temperatures shown are the surface temperature values on the top of the can and on the capacitor terminals. 当使用回流焊，在玻璃环氧树脂树脂基板上进行焊接的时候，产品顶部及端子部分温度，时间的推荐范围如下表所示。
2. Reflow should be performed twice or less 推荐回流次数不超过 2 次。
3. Please ensure that the capacitor became cold enough to the room temperature (5 to 35℃) before the second reflow. 请在第 1 次回流之后，必须确保电容器的温度已经完全冷却到室温(5~35℃)后方可进行第 2 次回流。



Note 备注:

1. Average ramp-up rate is 5°C/second max
温度上升平均每秒钟最多 5℃；
2. Ramp-down rate is 6°C/second max
温度下降平均每秒钟最多 6℃；
3. Time from 25°C to peak temperature is 6 minutes max.
从 25℃上升到峰值温度的时间最多 6 分钟；

Category 类别	Time maintained above 200°C (T1) 200℃以上时间	Time maintained above 217°C (T2) 217℃以上时间 (T2)	Time maintained above 230°C (T3) 230℃以上时间 (T3)	Range of Peak 峰值范围		Reflow number 回流焊次数
				Temp 温度	Times 时间	
Φ6.3	105sec.	90 sec.	60 sec.	260°C Max.	5sec Max.	2 times or less