



| REV. | DESCRIPTION | ECN NO. | NAME | DATE |
|------|-------------|---------|------|------|
|      |             |         |      |      |

技术要求 Specification:

1. 材质:磷青,表面镀锡  
Material: Phos. Bronze Tin-Plated  
镀层: Sn > 2.50um, Ni > 0.50um
2. 零件外观不得有有害毛刺、尖角、锐边和机械损伤;表面镀层应均匀、光亮、无雾斑、剥层等缺陷;  
Parts may not have the appearance of harmful burrs, sharp corners, sharp edges and mechanical damage, surface coating should be uniform, bright, no fog spots, delamination and other defects.
3. 适用线号: AWG#32-#28  
Wire range: AWG#32-#28

|                    |       |                                               |               |                |               |
|--------------------|-------|-----------------------------------------------|---------------|----------------|---------------|
| GENERAL TOLERANCE  |       | DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD |               |                |               |
| DIM. TOL.          |       | TITLE: GH1.25MM TERMINAL                      |               |                |               |
| X                  |       | DWG. NO.: WF-1C125B                           |               | DRAWN: MAX     |               |
| X.X                | ±0.30 | PART NO.: WF-1C125B                           |               | CHECKED: ELLA  |               |
| X.XX               | ±0.25 | UNIT: mm                                      |               | APPROVED: WILL |               |
| X.XXX              | ±0.15 | SCALE: none                                   | SHEET: 1 of 1 | DWG. SIZE: A4  | LAYER: bxconn |
| GENERAL ANGLE: ±3° |       |                                               |               |                |               |

