








RECOMMENDED P.C.B. LAYOUT
TOP VIEW (TOLRANCE: ± 0.05)



NOTES:

1. MATERIAL:

- 1.1 HOUSING:THERMOPLASTIC FLAMMABILITY RATING UL94-0
- 1.2 CONTACT:COPPERY ALLOY T=0.15MM
- 1.3 SHELL: COPPERY ALLOY T=0.25MM

2. FINISH:

2.1 CONTACT:

- 1U"MIN,PLATED ON CONTACT AREA
- G/F PLATING ON SOLDER TAIL AREA
- 50~80U" NICKEL UNDERPLATING OVERALL

2.2 SHELL:

- 80~120U" MATTER TIN PLAING ALL
- 50~80U" NICKEL UNDERPLATING OVERALL

3. SPECIFICATION:

- 3.3 CURRENT RATING:0.5A(2.3.4CONTACT)/1.8A (1.5CONTACT)MAX.
- 3.2 VOLTAGE:30 VAC
- 3.3 TEMPERATURE RANGE:-30°C~85°C
- 3.4 CONTACT RESISTANCE:30 MILLIONHM MAX.
- 3.5 DIELECTRIC WITHSTANDING VOLTAGE;250VAC R.M.S
- 3.6 INSULATION RESIS

05XX-4BH83-F
1:AU 1U"
6:AU 30U"
T:TIN
N:NICKEL
S:Scrolls F:Flat

		new		2015/5/3		A		瀚源		
ECN BO.		DESCRIPTION.		DATE.		REV.				
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1		
Mikey	Tom	Jerry	PART NAME	05XX-4BH83-F		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	05XX-4BH83-F				X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD					X.xx ±0.15	
				ANGULAIR ±3						
				FILE.NO.						