



PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

技术要求:

- 1、塑件材料:PA66
- 2、接触件:黄铜镀锡
- 3、接触电阻: $\leq 10m\Omega$
- 4、绝缘电阻: $\geq 1000M\Omega$
- 5、额定电压:250V AC DC
- 6、额定电流:2.0A AC DC
- 7、耐压:能承受1000V AC/Min ute
- 8、工作温度: $-25^{\circ}\sim\sim+85^{\circ}$
- 9、可焊性试验:浸锡面积 $\geq 95\%$ 温度 220^{+5}_{-0} ,时间 2.5 ± 0.5 秒
- 10、铅和镉等六大有害物质含量要符合环保要求

Part No	PIN	A	B	C
WF-1B200B2P-Y	2	2	6	
WF-1B200B3P-Y	3	4	8	2
WF-1B200B4P-Y	4	6	10	4
WF-1B200B5P-Y	5	8	12	6
WF-1B200B6P-Y	6	10	14	8
WF-1B200B7P-Y	7	12	16	10
WF-1B200B8P-Y	8	14	18	12
WF-1B200B9P-Y	9	16	20	14
WF-1B200B10P-Y	10	18	22	16
WF-1B200B11P-Y	11	20	24	18
WF-1B200B12P-Y	12	22	26	20
WF-1B200B13P-Y	13	24	28	22
WF-1B200B14P-Y	14	26	30	24
WF-1B200B15P-Y	15	28	32	26

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN,再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	黄色
序号	名称	材料	数量	附注
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL.		TITLE: WAFER 2.0mm H8.0mm 90° DIP 黄色		
X ±0.30		DWG. NO.: WF-1B200BNP-Y		
X.X ±0.25		DRAWN: MAX		
X.XX ±0.15		PART NO.: WF-1B200BNP-Y		
X.XXX ±0.15		CHECKED: ELLA		
GENERAL ANGLE: ±3°		APPROVED: WILL		
UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4
		LAYER: bxconn		

BXCONN®

