



REV.	DESCRIPTION	ECN NO.	NAME	DATE

PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

技术要求:

1. 塑件材料: PA66
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 1000M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $220 \pm 5^{\circ}\text{C}$, 时间 2.5 ± 0.5 秒
10. 铅和铜等六大有害物质含量要符合环保要求

Part No	PIN	A	B	C
WF-1A200B2P-Y	2	2	6	
WF-1A200B3P-Y	3	4	8	2
WF-1A200B4P-Y	4	6	10	4
WF-1A200B5P-Y	5	8	12	6
WF-1A200B6P-Y	6	10	14	8
WF-1A200B7P-Y	7	12	16	10
WF-1A200B8P-Y	8	14	18	12
WF-1A200B9P-Y	9	16	20	14
WF-1A200B10P-Y	10	18	22	16
WF-1A200B11P-Y	11	20	24	18
WF-1A200B12P-Y	12	22	26	20
WF-1A200B13P-Y	13	24	28	22
WF-1A200B14P-Y	14	26	30	24
WF-1A200B15P-Y	15	28	32	26

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN, 再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	黄色
序号	名称	材料	数量	备注

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD							
DIM.	TOL.	TITLE: WAFER 2.0mm H8.0mm 180° DIP 黄色							
X		DWG. NO.: WF-1A200BNP-Y							
X.X	± 0.30				DRAWN: MAX				
X.XX	± 0.25				CHECKED: ELLA				
X.XXX	± 0.15				APPROVED: WILL				
GENERAL	ANGLE: $\pm 3^{\circ}$	PART NO.: WF-1A200BNP-Y							
UNIT:	mm	SCALE:	none	SHEET:	1 of 1	DWG. SIZE:	A4	LAYER:	bxconn

