



REV.	DESCRIPTION	ECN NO.	NAME	DATE

PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

技术要求:

- 1、塑件材料:PA66 (UL-94V-0)
- 2、接触件:黄铜镀锡
- 3、接触电阻: $\leq 10m\Omega$
- 4、绝缘电阻: $\geq 1000M\Omega$
- 5、额定电压:250V AC DC
- 6、额定电流:2.0A AC DC
- 7、耐压:能承受1000V AC/Min ute
- 8、工作温度: $-25^{\circ} \sim +85^{\circ}$
- 9、可焊性试验:浸锡面积 $\geq 95\%$ 温度 220_{-0}^{+5} , 时间 2.5 ± 0.5 秒
- 10、铅和铜等六大有害物质含量要符合环保要求

Part No	PIN	A	B
WF-1B200A2P-R	2	2	6
WF-1B200A3P-R	3	4	8
WF-1B200A4P-R	4	6	10
WF-1B200A5P-R	5	8	12
WF-1B200A6P-R	6	10	14
WF-1B200A7P-R	7	12	16
WF-1B200A8P-R	8	14	18
WF-1B200A9P-R	9	16	20
WF-1B200A10P-R	10	18	22
WF-1B200A11P-R	11	20	24
WF-1B200A12P-R	12	22	26
WF-1B200A13P-R	13	24	28
...
WF-1B200A20P-R	20	(20-1)*2	(20+1)*2

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN,再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	红色
序号	名称	材料	数量	附注

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. TOL.		TITLE: WAFER 2.0mm H6.0mm 90° DIP 红绝			
X		DWG. NO.: WF-1B200ANP-R		DRAWN: MAX	
X.X	± 0.30	PART NO.: WF-1B200ANP-R		CHECKED: ELLA	
X.XX	± 0.25	UNIT: mm		APPROVED: WILL	
X.XXX	± 0.15	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
GENERAL ANGLE:	$\pm 3^{\circ}$				

BXCONN[®]

