



PRELIMINARY
DESIGN IS SUBJECT
TO CHANGE WITHOUT
PRIOR NOTICE

技术要求:

- 1、塑件材料:PA66
- 2、接触件:黄铜镀锡
- 3、接触电阻: $\leq 10m\Omega$
- 4、绝缘电阻: $\geq 1000M\Omega$
- 5、额定电压:250V AC DC
- 6、额定电流:2.0A AC DC
- 7、耐压:能承受1000V AC/Minute
- 8、工作温度: $-25^{\circ}\sim\sim+85^{\circ}$
- 9、可焊性试验:浸锡面积 $\geq 95\%$ 温度 $220 \pm 5^{\circ}$,时间 2.5 ± 0.5 秒
- 10、铅和铜等六大有害物质含量要符合环保要求

Part No	PIN	A	B	C
WF-1A200B2P-R	2	2	6	
WF-1A200B3P-R	3	4	8	2
WF-1A200B4P-R	4	6	10	4
WF-1A200B5P-R	5	8	12	6
WF-1A200B6P-R	6	10	14	8
WF-1A200B7P-R	7	12	16	10
WF-1A200B8P-R	8	14	18	12
WF-1A200B9P-R	9	16	20	14
WF-1A200B10P-R	10	18	22	16
WF-1A200B11P-R	11	20	24	18
WF-1A200B12P-R	12	22	26	20
WF-1A200B13P-R	13	24	28	22
WF-1A200B14P-R	14	26	30	24
WF-1A200B15P-R	15	28	32	26

2	Contact	Brass	n*1	电镀(锡): 整个表面镀底镍30u"MIN,再镀锡80u".MIN.
1	Wafer	PA66(UL94V-0)	1	红色
序号	名称	材料	数量	备注

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: WAFER 2.0mm H8.0mm 180° DIP 红色			
X		DWG. NO.: WF-1A200BNP-R		DRAWN: MAX	
X.X	± 0.30	PART NO.: WF-1A200BNP-R		CHECKED: ELLA	
X.XX	± 0.25	UNIT: mm		SCALE: none	
X.XXX	± 0.15	SHEET: 1 of 1		DWG. SIZE: A4	
GENERAL ANGLE:	$\pm 3^{\circ}$	LAYER: bxconn		APPROVED: WILL	