


Features

- ◇ Low cost
- ◇ Low leakage
- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ Easily cleaned with alcohol, Isopropanol and similar solvents
- ◇ The plastic material carries U/L recognition 94V-0

Mechanical Data

- ◇ Case: JEDEC TO-220AB, molded plastic
- ◇ Polarity: As marked
- ◇ Weight: 0.071ounce, 2.006 grams
- ◇ Mounting position: Any



Dimensions in millimeters

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.



Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.

		MUR 2005CT	MUR 2010CT	MUR 2015CT	MUR 2020CT	MUR 2040CT	MUR 2060CT	UNITS
Maximum recurrent peak reverse voltage	V _{RRM}	50	100	150	200	400	600	V
Maximum RMS voltage	V _{RMS}	35	70	105	140	280	420	V
Maximum DC blocking voltage	V _{DC}	50	100	150	200	400	600	V
Maximum average forw ard rectified current @T _C = 95 °C	I _{F(AV)}	20						A
Peak forw ard surge current 8.3ms single half-sine-w ave superimposed on rated load @T _J =125°C	I _{FSM}	125						A
Maximum instantaneous forw ard voltage @ 10A	V _F	0.975				1.3	1.5	V
Maximum reverse current @T _A =25°C at rated DC blocking voltage @T _A =150°C	I _R	5.0 250				10.0 500		μ A
Maximum reverse recovery time (Note1)	t _{rr}	25				50		ns
Operating junction temperature range	T _J	- 55 ----- + 150						°C
Storage temperature range	T _{STG}	- 55 ----- + 150						°C

NOTE: 1. Measured with $I_F = 0.5\text{A}$, $I_R = 1\text{A}$, $t_{rr} = 0.25\text{A}$.

Ratings AND Characteristic Curves

FIG.1 – TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC



NOTES: 1. RISE TIME = 7ns MAX INPUT IMPEDANCE = 1MΩ, 22pF.
2. RISE TIME = 10ns MAX SOURCE IMPEDANCE = 50Ω.

FIG.2 – TYPICAL FORWARD CHARACTERISTIC




FIG.3 – PEAK FORWARD SURGE CURRENT




FIG.4-FORWARD DERATING CURVE

