



SPECIFICATION

1. Rating : DC 12V 2A.
2. Contact resistance: ≤50mΩ.
3. Insulation resistance: ≥100MΩ (DC250V).
4. Withstanding voltage: 250VAC .
5. Insertion and extraction force: 5-35N
- 5.life test: 5000 cycles.
6. Operation temperature range: -25℃~85℃.
7. Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ±0.1	ANGULAR	1					
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
4	CONTACT FOOT	BRASS	1	Ni-PLATED	TITLE: DIN SOCKET			UNIT : MM	ROHS COMPLIANT	DWN		
3	CONTACT FOOT	BRASS	9	Ag-PLATED	MODEL: DIN-901			SCALE: 3:1	CHK'D			
2	COAT	BRASS	1	Ni-PLATED	东莞市六钧电子五金有限公司			APPD				
1	CASE	PBT	1	BLACK				PRO.AGL:		REV : A		
NO.	PART NAME	MATERIAL	QTY	FINISHING								