


■ Features

- High Current Rectifier Schottky Diode with Low VF Drop
- Low Voltage ,Low Inductance
- For Power Supply
- For Detection and Step-up-Conversion

■ Mechanical Data

- package:SOD-323
- Polarity: Color band denotes cathode end
- Mounting Position: Any.



■ Ordering Information

Part Number	Package	Marking	Packing	Quantity per reel	Reel Size
BAT60B	SOD-323	W5	Tape & Reel	3000 PCS	7 inches

■ Maximum Ratings & Thermal Characteristics(Ratings at 25℃ ambient temperature unless otherwise specified.)





Parameters	Symbol	Value	Unit
DC Blocking voltage	VR	10	V
Forward current	IF	3	A
Peak forward surge current 8.3 ms single half sine-wave	IFSM	5	A
Typical thermal resistance	RθJA	286	℃/W
Power Dissipation	PD	350	mW
Operating junction temperature	TJ	125	℃
Storage temperature range	TSTG	-65-+150	℃



■ **Electrical Characteristics**(Ratings at 25℃ ambient temperature unless otherwise specified)


Parameters	Symbol	Test conditions	Value			Unit
			Min	Typ	Max	
Forward voltage	VF	IF = 100mA IF = 500mA IF = 1000mA		0.33 0.41 0.45	0.38 0.50 0.60	V
Reverse breakdown voltage	V(BR)	IR=1mA	10			V
Maximum reverse current Tj=25℃	IR	VR=5V VR=8V			15 25	uA
Total capacitance	Ctot	VR = 5.0V, f = 1MHz		30		pF

■ **Typical Characteristics**





■ SOD-323 Package Outline Dimensions



Symbol	Min.(mm)	Max.(mm)
A		1.000
A1	0.000	0.100
A2	0.800	0.900
b	0.250	0.350
c	0.080	0.150
D	1.200	1.400
E	1.600	1.800
E1	2.500	2.700
L	0.475REF	
L1	0.250	0.400
θ	0°	8°