



Recommended PCB Layout

General Tolerance: ± 0.05

Solder Area



Specifications

Material

Insulator: Polymer, LCP 30% glass filled,
Natural, UL94V-0

Contact: Copper Alloy

Plating

Underplating: 30μ "- 50μ " Nickel all over
Contact Area: See ordering grid

Electrical

Current Rating: 3A per pin
Contact Resistance: 20 m Ω max.
Insulating Resistance: 1000 M Ω min.
Dielectric Withstand Voltage: 500V AC

Mechanical & Environmental

Operating Temperature: -40°C to +105°C

Soldering Process:




IR Reflow: 260°C for 10 secs
Manual Solder: 350°C for 3-5 secs

Mates with:

BG300 - Horizontal mating - Choose 5.4mm header pin length
BG306 - Perpendicular mating - Choose 4.0mm header pin length -
Higher MOQ may apply

NOTES:

Standard black version BG301 is BG080



CONTACTS	DIMENSIONS		
	A	B	C
02	5.08	2.54	5.50
03	7.62	5.08	7.50
04	10.16	7.62	7.50
05	12.70	10.16	7.50
06	15.24	12.70	7.50

Ordering Grid

BG301 - **XX** - **X** - **XXXX** - **L** - **B**

No. of Contacts
02 to 06

Contact Plating
A = Gold Flash All Over
B = Selective Gold Flash Contact Area/
Tin On Tail
C = Tin All Over
(Other plating options
available on request)

Packing Options
B = Tape and Reel with Cap
(MOQ 1,000 pcs on 5.4mm post length)
(check with GCT for MOQ on 4.0mm post length)

Insulator Material
L = LCP (Natural)



Dimension D - Post Length
0400 = 4.00mm (Standard when mating with BG306)
0540 = 5.40mm (Standard when mating with BG300)
or Specify Custom Post Length
eg 0250 = 2.50mm
(Maximum 3000=30.00mm)
(Minimum 0100=1.00mm)

Request Samples
and Quotation



Part Number BG301		Product Description 2.54mm Pitch Pin Header, Single Row, Surface Mount, Horizontal, without Locating Peg, Natural LCP	
Drawing Date 7th December 2011			
By CC	CC	Tolerances (Except as Noted) Length Angle	Units: Metric (mm)
Detail BG301 C PCN		X.X $\pm$ 0.30 X.XX $\pm$ 0.20	
Revision C5			
Date 24/02/21			
			This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE
		Not to Scale	Drawn By CM Sheet No. 1/2

GCT
www.gct.co



2 PIN





3 PIN





4 PIN



5 PIN




6 PIN



PINS	UNITS/REEL	REELS PER CARTON	CARTON	TOTAL CARRIER TAPE LENGTH
2 & 3	1000 PCS	16	16,000	16.5 m
4	1000 PCS	10	10,000	20.7 m
5 & 6	1000 PCS	10	10,000	16.5 m

FOR 5.40mm PIN LENGTH ONLY

See table for
number of reels
per carton

Reel

Vacuum Bag

Transparent
Glue Tape

L=390

W=390

H=400
Outside

Part Number BG301		Product Description 2.54mm Pitch Pin Header, Single Row, Surface Mount, Horizontal, without Locating Peg, Natural LCP	
Drawing Date 7th December 2011			
By CC	Tolerances (Except as Noted) Length	Angle	Units: Metric (mm)
Detail BG301 C PCN			
Revision C5			
Date 24/02/21			



This drawing is confidential and
copyright of Global Connector
Technology, Ltd (GCT).
This drawing must not be copied
or disclosed without written
consent. E & OE

GCT
www.gct.co

Not to
Scale

Drawn By
CM

Sheet No.
2/2