



4.20 [0.165]



①



SECTION A-A  
SCALE 1:1



SECTION B-B  
SCALE 1:1



SECTION C-C  
SCALE 1:1

Specifications:

规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:10A AC/DC  
额定电流: 10A AC/DC  
Withstanding voltage:1500V AC/minute  
耐受电压: 1500V AC/分钟  
Temperature range:-25°C +85°C  
温度范围: -25°C +85°C  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance:≤10mΩ  
接触电阻: ≤10mΩ  
After environmental testing:≤20mΩ  
环境测试后: ≤20兆欧

X5050 T F-B SN X -X  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:  
T-Terminal
- ③ Welding Board Angle:  
M-Male
- ④ Material:  
B-Brass
- ⑤ Plating Category:  
SN-Bright Tin Plating
- ⑥ Plating Way:  
Blank-stamping before plating  
B-plating before stamping
- ⑦ Mold No/MARK&Special No

广东星坤科技股份有限公司

生 日期  
發

文件工程章

REVISIONS  
www.helxbk.com



X5050TF-BSNB	Barss	AWG#16-20	2.50mm(Max)	Plating Before Stamping: 10u"Min Ni 30u"Min Sn	X5050HM
X5050TF-BSN	Barss	AWG#16-20	2.50mm(Max)	Stamping Before Plating: 30-50u" Ni 70-120u" Sn	X5050HM
PATR NO	Material	Wire Range	Insulation O.D	Finish	Suitable XKB Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE: X5050TF-BSNB
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/mn	5.08 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
UNSPECIFIED TOLERANCES			WEIGHT
XKB INDUSTRIAL PRECISION CO.,LIMITED			SHEET
			REVISION
			1.0g
			1/1
			A0