








SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage : 250VAC .
- 5.Operating Force: $160 \pm 50\text{gf}$
- 6.life test:100,000 cycles.
- 7.operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

CIRCUIT DIAGRAM

H=2.0

P.C.B LAND DIMENSION

					TOLERANCE UNLESS SPECIFIED						
6	KAPTON	POLYIMIDE	1	YELLOW	UP TO 5mm: ± 0.1	ANGULAR	1				
5	TERMINAL	PHOSPHOR BRONZE	2	Ag-Plated	ABOVE 5mm: ± 0.2	$\pm 1^{\circ}$	NO	DATE	REVISIONS		BY APPD
4	SPRING	STEEL	1	Ag-Plated	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN	
3	COVER	SUS	1		MODEL: TS-1185-020A			SCALE: 1:1		CHK'D	
2	CASE	LCP	1							APPD	
1	KNOB	LCP	1								
NO.	PART	NAME	MATERIAL	QTY	FINISHING			PRO.AGL: 			

东莞市六钧电子五金有限公司

REV :A0