


[illegible]

Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)

P	3	D	2	22	1	5	00	4	2206
产品类型 P=排针	间距 3=2.54	塑胶高度 D=2.5	排数 2=双排	单排PIN数 1~40P	产品形态 1=DIP	塑胶材料 1=PBT 2=PC 5=PA6T	电镀厚度 00=常规 1=1u" 02=2u" 03=3u"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装	序列号



				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10				SHEET	1/1	PART NO.	1010301439
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	±3°	APPROVE			PROJ.		TITLE:	2.54PH H=2.5 2*22P DIP PA6.0 PC3.0 L=11.5 AU0.6U PA6T
				DIM	TOL							