

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass





Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 5 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P 2 C 2 12 1 5 00 X 1611

产品类型
P=排针

间距
2=2.0

塑胶高度
C=2.0

排数
2=双排

单排PIN数
2~40P

产品形态
1=DIP

塑胶材料
2=LCP
5=PA6T

电镀厚度
00=常规
01=AU1U

包装方式
1=管装
2=卷装
3=盘装
4=袋装
5=盒装

序列号

Dimension antitheses list

ITEM	PA	PB	PW	PC	L	H	W
001	3.9			2.8	8.7	2.0	4.0
Alternate							

OPERATION

X.X ±0.30

X.XX ±0.20

X.XXX ±0.10

Angle ±3°

DIM TOL

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

深圳市连盛精密连接器有限公司

PART NO.

1010200421

TITLE:

2.0PH H=2.0 2x12P DIP PA3.9
PC2.8 L=8.7 AU0.6U PA6T

1

2

3

4

5

6

7

8

9