



Plastic-Encapsulate Diodes


SCHOTTKY BARRIER DIODE

FEATURES


- ♦ For low-loss, fast-recovery, meter protection, bias isolation and clamping applications
- ♦ Integrated diffused guard ring
- ♦ Low forward voltage



BAT64-06 MARKING:66S



BAT64-05 MARKING:65S



BAT64-04 MARKING: 64S

BAT64-06	BAT64-05	BAT64-04

Solid dot = Green molding compound device, if none, the normal device.





Maximum Ratings @Ta=25°C

Parameter	Symbol	Limits	Unit
Peak reverse voltage DC reverse	V_{RM} V_R	40	V
Non-repetitive Peak forward surge current @t=8.3ms	I_{FSM}	0.8	A
Forward current	I_F	0.25	A
Power Dissipation	P_D	250	mW
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	400	°C/W
Operating Junction Temperature Range	T_j	-40 ~ +125	°C
Storage Temperature Range	T_{stg}	-55 ~ +150	°C

Electrical Ratings @Ta=25°C

Parameter	Test Conditions	Symbol	Min.	Typ.	Max.	Unit
Reverse breakdown voltage	$I_R=10\mu A$	V_R	40			V
Forward voltage	$I_F=1mA$ $I_F=10mA$ $I_F=30mA$ $I_F=100mA$	V_F			350 430 520 750	mV
Reverse current	$V_R=25V$	I_R			2	μA
Capacitance between terminals	$V_R=1V, f=1MHz$	C_T		6		pF


Typical Characteristics



Package Outline

SOT-23

Plastic surface mounted package; 3 leads



Symbol	Dimension in Millimeters	
	Min	Max
A	0.95	1.40
B	1.78	2.04
bp	0.35	0.50
C	0.08	0.19
D	2.70	3.10
E	1.20	1.65
HE	2.20	3.00
A1	0.100	0.013
Lp	0.20	0.50

Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
SOT-23	Tape/Reel, 7" reel	3 000	EIA-481-1