

# H3-MABA-011062

1-300MHz 75Ω 1:2 Balun


## APPLICATIONS

Ideally suited for all CATV Broadband and FTTx applications.

## FEATURES


- Surface mount
- Impedance ratio: 1:2
- Centre tap on secondary
- RoHS compliant and Pb free
- Available on tape and reel
- 260° reflow compatible

## DIMENSIONS



A	B	C
4.23	3.74	3.61
D		
1.27		

## Land Pattern



E	F	G
4.83	3.30	1.40
H	J	
0.76	1.27	


Unless otherwise stated dimensions are in mm

Tolerance: .xx ± 0.25, .xxx ± 0.05

## ELECTRICAL SPECIFICATIONS@25°C:

Parameters (P#: ENA PORT)	frequency band	Min.	Typ.	Max.	Unit
Port Impedance, Z0			75		Ohm
Impedance Ratio			1:2		
Insertion Loss 1 (Pin1 - Pin3)	1 - 300 MHz		0.5	0.8	dB
Insertion Loss 2 (Pin1 - Pin5)	1 - 200 MHz		0.5	0.8	dB
	200 - 300 MHz		0.7	1	dB
Input Return Loss(Pin 1)	1-5MHz	14	18.0		dB
	5-300MHz	17.0	19.0		dB
Amplitude Balance	1 - 180 MHz		0.02	0.2	dB
	180 - 300 MHz		0.20	0.5	dB
Phase Balance(ref value 180°)	1 - 150 MHz		0.50	2.0	Deg
	150 - 300 MHz		1.0	4.0	Deg

## FUNCTIONAL SCHEMATIC



## PIN CONFIGURATION

Pin No.	Function
1	Primary Dot (input)
2	Primary (ground)
3	Secondary (Output1)
4	Center Tap (Ground)
5	Secondary Dot (Output2)

## ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Input RF Power	2000mW Max
DC Current	1500mA Max
Operating Temperature Range	-40 to 125°C

Tel: +86-28-85589664


E-mail: mr\_li@henglitaitech.com

Web: www.hltchips.com


Adress:No.198 Tianqin East Street, Gaoxin West District, Chengdu City

## TEST CURVE


Insertion Loss: Pin 1 to Pin 3




Insertion Loss: Pin 1 to Pin 5



Amplitude Balance



Phase Balance



Input Return Loss: Pin 1

