


Super Fast Rectifiers
Reverse Voltage - 600V
Forward Current - 10A
FEATURES

- ◆Glass passivated chip junctions
- ◆Super fast recovery time for switching mode application
- ◆High Forward Surge Capability
- ◆Low Reverse Current
- ◆Lead free in compliance with EU RoHS 2011/65/EU directive

MECHANICAL DATA

- ◆Circuit figure: Common Cathode
- ◆Leads: Solderable per mil-std-202, Method 208
- ◆Polarity: as marked
- ◆Mounting torque: 5 in-lbs maximum
- ◆Terminals: Puretin plated
- ◆Weight: TO-263(D²PAK) 1.35 grams


MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (TA=25°C)

RATINGS	SYMBOL	Value	Units
Maximum repetitive reverse voltage	V_{RRM}	600	V
Maximum RMS voltage	V_{RMS}	420	V
Maximum DC blocking voltage	V_{DC}	600	V
Maximum average forward current	I_{AV}	10	A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	150	A
Typical thermal resistance per diode (Note 1)	$R_{\theta-JC}$	2.5	°C/W
Operation Junction Temperature and Storage Temperature	T_J, T_{STG}	-55 ~ +150	°C
CHARACTERISTICS			
Typical forward voltage per leg at 5A	V_F	1.7	V
Maximum average reverse current at rated DC blocking voltage $T_J=25^{\circ}C$ $T_J=125^{\circ}C$	I_R	5 250	μA
Typical reverse recovery time (Note 2)	T_{RR}	35	nS

Notes: 1. Thermal resistance from junction to case.
2. Test conditions: $I_F=0.5A$, $I_R=1.0A$, $I_{RR}=0.25A$.

Ratings And Characteristic Curves

FIG. 1 - TYPICAL FORWARD CURRENT DERATING CURVE




FIG. 3 - MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 4 - TYPICAL REVERSE CHARACTERISTICS




FIG. 2 - TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS






FIG.6- TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTICS



Package outline Dimensions in millimeters

TO-263

