

Specification Sheet

Part Number: 133-00059



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

1-Piece Cable Tie & Edge Clip, 3.5" Long, EC5, Panel Thickness 0.04 - 0.12", 50 lb, PA66HS, Black, 500/bg

Article Number

133-00059

Type

T40XEC5SP-E

Color

Black (BK)

Quantity Per

bag

Product Description

HellermannTyton's Cable Tie with Edge Clip is designed to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. This fastener is molded as a one-piece clip and tie combination.

Short Description

1-Piece Cable Tie & Edge Clip, 3.5" Long, EC5, Panel Thickness 0.04 - 0.12", 50 lb, PA66HS, Black, 500/bg

Global Part Name	T40XEC5SP-E-PA66HS-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	40.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	178
-----------------------------------	-----

Length L (Imperial)	3.5
---------------------	-----

Length L (Metric)	85.0
-------------------	------

Fixation Method	Edge Clip
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.16
--------------------	------

Width W (Metric)	4.0
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	0.6
--------------------------------	-----

Bundle Diameter Max (Metric)	15.0
------------------------------	------

Height H (Imperial)	0.05
Height H (Metric)	1.2
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).