

Specification Sheet

Part Number: 111-95278



The 304 grade stainless steel offers excellent resistance to corrosion, weather and chemicals.
Self-locking, ball bearing mechanism ensures reliable performance and easy insertion.
Fully enclosed head prevents debris from interfering with locking mechanism.
High tensile strength for dependability and safety in heavy duty applications.

Stainless Steel Tie, 26.8" Long, 607lb Tensile Strength, SS304, Metal, 50/pkg

Article Number	111-95278
Type	MBT27XHS
Color	Metal (ML)
Quantity Per	bag
Product Description	HellermannTyton’s Stainless Steel Ties are designed with a ball bearing locking mechanism to ensure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Stainless steel provides protection when used in corrosive environments, fire resistance and temperature extremes.

Short Description	Stainless Steel Tie, 26.8" Long, 607lb Tensile Strength, SS304, Metal, 50/pkg
Global Part Name	MBT27XHS-SS304-ML
Minimum Tensile Strength (Imperial)	607.0
Minimum Tensile Strength (Metric)	2700.0
Length L (Imperial)	26.8
Length L (Metric)	681.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	ball bearing lock
Variant	Not Serrated
Width W (Imperial)	0.48
Width W (Metric)	12.3
Bundle Diameter Min (Imperial)	0.67
Bundle Diameter Min (Metric)	17.0
Bundle Diameter Max (Imperial)	8.0
Bundle Diameter Max (Metric)	203.0

Thickness T (Imperial)	0.01
Thickness T (Metric)	0.3
Material	Stainless Steel (SS304)
Material Shortcut	SS304
Flammability	Non-burning
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	7326908695

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)