

CODACA

Molding Power Choke
CSAB0530 Series



Construction Wire



Outline:

- Magnetic shielded structure:excellent resistance to electro Magnetic interference (EMI)
- A composite structure,ultra low buzz noise
- Low loss,high efficiency,wide application frequency
- Lightweight design,save space,suitable for high density SMT

Features:

- Core material: Alloy powder
- Environmental: RoHS, Reach compliant ,Halogen free
- Weight:0.420g
- Moisture Sensitivity:Level (MSL) 1 (unlimited floor life at 5 ~ 40℃, RH≤ 70% relative humidity).
- Operating temperature range: -40℃ ~ +125℃ (including coil's self temperature rise)
- Storage temperature range: -40℃～+125℃

Application:

- PDA/notebook/desktop/server applications
- DC /DC converters for entertainment/navigations systems
- Noise suppression for motors:windshield wipers/power seats/Power Mirrors/heating and ventilation blower/ HID lighting

1 Electrical Characteristics

Part No.	Inductance (μH)※1	D.C.R. (mΩ)		Isat (A)※2	Irms (A) ※3
	±20%	Typical	Max.	Typical	Typical
CSAB0530-R22M	0.22	3.30	4.00	19.0	16.3
CSAB0530-R33M	0.33	4.80	5.60	15.0	13.5
CSAB0530-R47M	0.47	8.80	11.0	14.0	10.0
CSAB0530-R68M	0.68	9.30	12.0	12.0	9.70
CSAB0530-1R0M	1.00	11.7	14.0	12.0	8.70
CSAB0530-1R5M	1.50	16.2	23.0	12.0	7.40
CSAB0530-2R2M	2.20	25.5	29.0	9.50	5.90
CSAB0530-3R3M	3.30	35.8	42.0	6.00	5.00
CSAB0530-4R7M	4.70	52.4	60.0	5.00	4.10
CSAB0530-5R6M	5.60	57.1	65.0	4.50	3.90
CSAB0530-6R8M	6.80	82.0	90.0	4.00	3.30
CSAB0530-8R2M	8.20	109	120	4.00	2.80
CSAB0530-100M	10.0	117	125	4.00	2.60
CSAB0530-150M	15.0	171	210	3.00	2.40
CSAB0530-220M	22.0	190	248	2.30	2.00


All data is tested on 25℃ ambient temperature

1.Inductance measure condition at 100kHz,1.0V

2.Isat:the actual value of DC current when the inductance decrease 30% of its initial value

3.Irms:the actual value of DC current when the temperature rise is ΔT40℃(Ta=25℃)

2 Product Dimensions (mm)



Typical Land Pattern

3 How to Order:

CSAB0530-100M

Model

Dimensions

Value Code

CODACA ELECTRONIC CO., LTD


TEL: +86 755 89585372 FAX: +86 755 89585280


http://www.codaca.com E-mail: info@codaca.com


This product is not authorized for use in any application related to safety.
Specification subject to change without notice. Please check web site for latest information.


Revised: 07/14/2020


4 Saturation Current vs Temperature Rise Current Curve



























CSAB0530-4R7M
L(μH)
ΔT(℃)
5.60
4.80
4.00
3.20
2.40
1.60
0.80
0.00
70
60
50
40
30
20
10
0
0.0
1.4
2.8
4.2
5.6
7.0
Idc(A)



CSAB0530-5R6M
L(μH)
ΔT(℃)
6.30
5.40
4.50
3.60
2.70
1.80
0.90
0.00
70
60
50
40
30
20
10
0
0.0
1.2
2.4
3.6
4.8
6.0
Idc(A)


CSAB0530-6R8M
L(μH)
ΔT(℃)
8.40
7.20
6.00
4.80
3.60
2.40
1.20
0.00
70
60
50
40
30
20
10
0
0.0
1.0
2.0
3.0
4.0
5.0
Idc(A)


CSAB0530-8R2M
L(μH)
ΔT(℃)
10.50
9.00
7.50
6.00
4.50
3.00
1.50
0.00
70
60
50
40
30
20
10
0
0.0
1.0
2.0
3.0
4.0
5.0
Idc(A)



CSAB0530-100M
L(μH)
ΔT(℃)
14.00
12.00
10.00
8.00
6.00
4.00
2.00
0.00
70
60
50
40
30
20
10
0
0.0
1.0
2.0
3.0
4.0
5.0
Idc(A)


CSAB0530-150M
L(μH)
ΔT(℃)
21.00
18.00
15.00
12.00
9.00
6.00
3.00
0.00
70
60
50
40
30
20
10
0
0.0
0.7
1.4
2.1
2.8
3.5
Idc(A)



CSAB0530-220M
L(μH)
ΔT(℃)
28.00
24.00
20.00
16.00
12.00
8.00
4.00
0.00
70
60
50
40
30
20
10
0
0.0
0.6
1.2
1.8
2.4
3.0
Idc(A)

5 L vs Frequency


CSAB0530-R22M




CSAB0530-R33M




CSAB0530-R47M




CSAB0530-R68M




CSAB0530-1R0M




CSAB0530-1R5M




CSAB0530-2R2M




CSAB0530-3R3M




CSAB0530-4R7M




CSAB0530-5R6M




CSAB0530-6R8M




CSAB0530-8R2M




CSAB0530-100M



CSAB0530-150M




CSAB0530-220M




6 Impedance vs Frequency


CSAB0530-R22M




CSAB0530-R33M




CSAB0530-R47M




CSAB0530-R68M




CSAB0530-1R0M




CSAB0530-1R5M




CSAB0530-2R2M




CSAB0530-3R3M




CSAB0530-4R7M




CSAB0530-5R6M




CSAB0530-6R8M




CSAB0530-8R2M




CSAB0530-100M



CSAB0530-150M




CSAB0530-220M




7 Packing Specification


7.1 Carrier Tape Dimensions (mm)



※ Packing is referred to the international standard IEC 60286-3.

7.2 Reel Dimensions (mm)






7.3 Carton Dimensions and Packing Quantity

■ Inner Carton：340×340×95mm ■ Outer Carton ：360×360×370mm

Product Series	Quantity / Reel	Inner Carton Quantity	Outer Carton Quantity
CSAB0530	2000pcs	(2000×4) = 8000pcs	(8000×3) = 24000pcs

8 Soldering Specification

8.1 Reflow Profile for SMT Components



8.2 Classification of Peak Package Body Temperature (T_P)

	Package Thickness	Package Volume		
		<350 mm^3	350～2000 mm^3	>2000 mm^3
PB-Free Assembly	<1.6mm	260℃	260℃	260℃
	1.6～2.5mm	260℃	250℃	245℃
	≥2.5mm	250℃	245℃	245℃

※ Reflow is referred to standard IPC/JEDEC J-STD-020E.

9 Notice of Use

9.1 Special remind:Circuit design, component placement, PCB size and thickness, cooling system and etc. all will affect the product temperature. Please verify the product temperature in the final application.

9.2 Product in packing storage condition:temperature 5 ~ 40℃, RH≤ 70%.
If taking out for use, the remaining products should be sealed in plastic bags and preserved in accordance With the above conditions, to avoid oxidation of terminals (electrodes), affecting soldering status.

9.3 A storage of Codaca Electronic products for longer than 12 months is not recommended, Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.

9.4 Do not keep products in unsuitable storage conditions, such as areas susceptible to high temperatures, high humidity, dust or corrosion.

9.5 Always handle products with care.

9.6 Don't touch electrodes directly with bare hands as oil secretions may inhibit soldering. Always ensure optimum conditions for soldering.

9.7 When this product will be used on a similar or new project to the original one, sometimes it might be unable to satisfy the specifications due to different condition of usage.

9.8 This inductor itself does not have any protective function in abnormal condition, such as overload, short-circuit, open-circuit conditions, etc. Therefore, it shall be confirmed that there is no risk of smoke, fire, dielectric withstand voltage, insulation resistance, etc., or use in abnormal conditions protective devices or protection circuit in the end product.

9.9 Hi-Pot test with higher voltage than spec value will damage insulating material and shorten its life.

9.10 If using in potting compound, the magnet wire coating might be damaged, please consult with us.

9.11 Refrain from rinsing product. If necessary, please consult with us.

*9.12 Codaca Electronic products without "V" prefix are qualified for industrial product requirement , and with "V" prefix are qualified for AEC-Q200, but it doesn't mean that Codaca Electronic products can absolutely meet specific industry norms and quality test standards in automotive electronics or more strict application fields . Codaca Electronic will be exempted from being responsible for the consequences of using Codaca products in automotive electronic or higher application field related to safety when without being aware of it.