

GaN 650V GaN HEMT

RC65E300Y


Description

The RC65E300Y Series 650V,300mΩ gallium nitride (GaN) FETs are normally-off devices. RealChip GaN FETs offer better efficiency through lower gate charge,faster switching speeds, and smaller reverse recovery charge, delivering significant advantages over traditional silicon(Si) devices.


RealChip is a leading-edge wide band gap supplier with world-class innovation.

Ordering Information

Part Number	Package	Package Configuration
RC65E300Y	DFN5*6-8L	Source




Top



Bottom

Application

- Fast charger
- Renewable energy
- Telecom and data-com
- Servo motors
- Industrial
- Automotive



Circuit Symbol

General Features

Low conduction and switching losses no free-wheeling diode required RoHS compliant and Halogen-free

Features

BV_{DSS}	$R_{DS(on)}$	I_{DS}	Q_G
650V	300mΩ	8A	1.35nC

Benefits

- Increased efficiency through fast switching
- Increased power density
- Reduced system size and weight

GaN 650V GaN HEMT

RC65E300Y

Absolute Maximum Ratings

$T_j=25^\circ\text{C}$ unless otherwise stated

Symbol	Parameter	Limit value	Unit
$V_{DS,\text{max}}$	Drain to source voltage($T_j=-55^\circ\text{C}$ to 150°C)	650	
$V_{DS(\text{transient})}$	Drain to source voltage-transient ^a	750	V
V_{GS}	Gate to source voltage	-10~+7	
I_D	Continuous drain current @ $T_C=25^\circ\text{C}$ ^b	8	A
	Continuous drain current @ $T_C=125^\circ\text{C}$ ^b	3.5	
I_{DM}	Pulse drain current (pulse width: 300μs) @ $T_C=25^\circ\text{C}$	11	
	Pulse drain current (pulse width: 300μs) @ $T_C=125^\circ\text{C}$	6	
P_D	Maximum power dissipation @ $T_C=25^\circ\text{C}$	38	W
T_C	Operating temperature	Case	$^{-55\sim150}$ °C
T_J		Junction	$^{-55\sim175}$ °C
T_S	Storage temperature		$^{-55\sim150}$ °C

Notes:

a. Non-repetitive events, $T_{\text{pulse}} < 200\mu\text{s}$

b. For increased stability at high current operation

GaN 650V GaN HEMT

RC65E300Y

Thermal Resistance

Symbol	Parameter	Limit value	Unit
$R_{\theta_{JC}}$	Junction-to-case	3.3	°C/W

GaN 650V GaN HEMT

RC65E300Y

Electrical Parameters

$T_j=25^\circ\text{C}$ unless otherwise stated

Symbol	Parameter	Min	Typ	Max	Unit	Test Conditions
Forward Device Characteristics						
$V_{(\text{BL})\text{DSS}}$	Drain-source voltage	650	-	-	V	$V_{GS}=0\text{V}$
$V_{GS(\text{th})}$	Gate threshold voltage	2	2.5	3	V	$I_D=10\mu\text{A}/\text{mm}, V_{DS}=1\text{V}, T_j=25^\circ\text{C}$
	Gate threshold voltage	-	2.8	-	V	$I_D=10\mu\text{A}/\text{mm}, V_{DS}=1\text{V}, T_j=150^\circ\text{C}$
$R_{DS(\text{on})}$	Drain-source on resistance	-	300	360	$\text{m}\Omega$	$V_{GS}=6\text{V}, I_D=1\text{A}, T_j=25^\circ\text{C}$
		-	660	-		$V_{GS}=6\text{V}, I_D=1\text{A}, T_j=150^\circ\text{C}$
I_{DSS}	Drain-to-source leakage current	-	1	10	μA	$V_{DS}=650\text{V}, V_{GS}=0\text{V}, T_j=25^\circ\text{C}$
		-	10	50		$V_{DS}=650\text{V}, V_{GS}=0\text{V}, T_j=150^\circ\text{C}$
I_{GSS}	Gate-to-source forward leakage current	-	60	-	μA	$V_{GS}=6\text{V}, V_{DS}=0\text{V}$
C_{ISS}	Input capacitance	-	46	-		
C_{OSS}	Output capacitance	-	18	-	pF	$V_{GS}=0\text{V}, V_{DS}=400\text{V}, f=1\text{MHz}$
C_{RSS}	Reverse capacitance	-	0.7	-		
$C_{o(er)}$	Effective output capacitance (energy related)	-	27	-	pF	$V_{GS}=0\text{V}, V_{DS}=0 \text{ to } 400\text{V}$
$C_{o(tr)}$	Effective output capacitance (time related)	-	40	-	pF	$V_{GS}=0\text{V}, V_{DS}=0 \text{ to } 400\text{V}$
Q_{OSS}	Output Charge	-	16	-	nC	$V_{GS}=0\text{V}, V_{DS}=0 \text{ to } 400\text{V}$
Q_G	Total gate charge	-	1.35	-		
Q_{GS}	Gate-source charge	-	0.15	-	nC	$V_{DS}=400\text{V}, V_{GS}=0 \text{ to } 6\text{V}, I_D=1\text{A}$
Q_{GD}	Gate-drain charge	-	0.5	-		
$t_{d(on)}$	Turn-on delay time	-	4.4	-		
$t_{d(off)}$	Turn-on delay time	-	4.1	-		
t_r	Rise time	-	11.8	-		
t_f	Fall time	-	11.2	-		
Reverse Device Characteristics						
V_{SD}	Reverse voltage	-	3	-	V	$V_{GS}=0\text{V}, I_{SD}=3\text{A}$
Q_{RR}	Reversere recovery charge	-	0	-	nC	$I_{SD}=3\text{A}, V_{DS}=400\text{V}$

GaN 650V GaN HEMT

RC65E300Y

Electrical Characteristics

$T_j=25^\circ\text{C}$ unless otherwise stated




Figure 1. Typical Output Characteristics $T_j=25^\circ\text{C}$




Figure 2. Typical Output Characteristics $T_j=125^\circ\text{C}$




Figure 3. Drain-source On-state Resistance




Figure 4. Typical Transfer Characteristics $V_{DS}=1\text{V}$

GaN 650V GaN HEMT

RC65E300Y

Electrical Characteristics

$T_j=25^\circ\text{C}$ unless otherwise stated




Figure 5. Drain-source Leakage Characteristics




Figure 6. Typical On-state Resistance $T_j=25^\circ\text{C}$




Figure 7. Typical Capacitance $f=1\text{MHz}$




Figure 8. Typical Gate Charge ($V_{DS}=400\text{V}$, $I_D=1\text{A}$)

GaN 650V GaN HEMT

RC65E300Y

Electrical Characteristics

$T_J=25^\circ\text{C}$ unless otherwise stated




Figure 9. Typical Output Charge $f=1\text{MHz}$




Figure 10. Typical Coss Stored Energy $f=1\text{MHz}$




Figure 11. Power Dissipation




Figure 12. Transient Thermal Impedance

GaN 650V GaN HEMT RC65E300Y

Electrical Characteristics




Figure 13. Safe Operation Area At $T_c=25^\circ\text{C}$




Figure 14. Safe Operation Area At $T_c=125^\circ\text{C}$




Figure 15. Switching Times With Inductive Load

$V_{DS}=400\text{V}$, $V_{GS}=0\text{V}$ to 6V , $I_D=3\text{A}$,
 $R_{G-on(ext)}=6.8\Omega$, $R_{G-off(ext)}=2.2\Omega$, $L=250\mu\text{H}$




Figure 16. Switching Times With Waveform


GaN 650V GaN HEMT

RC65E300Y


PACKAGE DIMENSIONS

DFN5*6-8L

Top view



Bottom view



Side view(left/right)



Symbol	Min. (mm)	Mean. (mm)	Max. (mm)
A	0.85	0.90	0.95
A1	0	0.02	0.05
A2	0.203REF		
D	5.9	6	6.1
E	4.9	5	5.1
D1	0.43	0.53	0.63
D2	2.27	2.37	2.47
D3	1.8	1.9	2
E1	3.65	3.75	3.85
E2	4.16	4.26	4.36
E3	0.27	0.37	0.47
E4	0.27	0.37	0.47
b	0.4	0.45	0.5
e	1.17	1.27	1.37
L	0.5	0.6	0.7