




Signal Relay Series 信号继电器系列 --JY23F

FEATURES特点

- 3A Amps super miniature relay
3A超小型继电器
- 1kV dielectric strength (between coil and contacts)
线圈与触点间介质耐压1kV
- 1 Form C configurations
具有一组转换触点形式
- Overall dimensions (12.3X7.4X10.1)mm
外形尺寸 (12.3X7.4X10.1) mm



CONTACT PARAMETERS触点参数

Contact Form触点形式	C-1Form C
Rating Load (Resistive) 额定负载 (阻性)	3A 125VAC/30VDC
Max. Switching Current最大切换电流	3A
Max.Switching Voltage最大切换电压	250VAC
Max.Switching Power最大切换功率	750VA/90W

CHARACTERISTICS性能参数

Contact Materials触点材料	Ag Alloy银合金	
Contact Resistance接触电阻	50 mΩ Max	
Operate Time吸合时间	5ms.Max	
Release Time释放时间	5ms.Max	
Insulation Resistance绝缘电阻	100MΩ Min.(DC500V)	
Initial Dielectric Strength介质耐压	between open contacts: 触点与触点间:	AC500V,50/60Hz 1Min
	between contacts and coil: 触点与线圈间:	AC1000V,50/60Hz 1Min
Vibration Resistance抗振动	Damage limits: 耐久:	10~55Hz Double Amplitude双振幅1.5mm
	Malfunction: 误动作:	10~55Hz Double Amplitude双振幅1.5mm
Shock Resistance抗冲击	Damage limits: 耐久:	100G Min
	Malfunction: 误动作:	10G Min
Life寿命	Mechanical Life (10800 per hour) 机械寿命 (每小时10800次)	1×10 ⁷
	Electrical Life (1800 per hour) 电气寿命 (每小时1800次)	1×10 ⁵
Ambient Temperature环境温度	-40 °C ~ +70 °C (No condensation) (不冷凝)	
Unit Weight单位重量	约Approx.2.2g	



COIL RATINGS (at23°C) 线圈参数 (在23°C)

Coil Nominal Voltage 额定电压 (VDC)	Nominal Current 额定电流 ±10(mA)	Coil Resistance 线圈电阻 ±10% (Ω)	Max. Continuous Voltage 最大连续外加电压	Pick-Up Voltage 吸合电压 (Max)	Drop-Out Voltage 释放电压 (Min)	Rated power 额定功率
3	50.00	60	Coil Nominal Voltage 150% 额定电压的 150%	Coil Nominal Voltage 75% 额定电压的 75%	Coil Nominal Voltage 10% 额定电压的 10%	0.15 W
5	30.12	166				
6	25.00	240				
9	16.67	540				
12	12.50	960				
24	6.25	3,840	Coil Nominal Voltage 150% 额定电压的 150%	Coil Nominal Voltage 75% 额定电压的 75%	Coil Nominal Voltage 5% 额定电压的 5%	0.20 W
3	66.67	45				
5	40.00	125				
6	33.33	180				
9	22.22	405				
12	16.67	720				
24	8.33	2,880				

ORDERING INFORMATION 订货标记

JY23F-S-DC12V-C-L-(XXX) 1 2 3 4 5 6	
1. Model Number 基本型号 JY23F	4. Contact Form: C-1Form C 触点形式: C-1组转换
2. Encapsulation form: S-Plastic Sealed SH:Fluk proofed 封装形式: S-塑封型 SH-防助焊剂型	5. Coil Power: L- sensitive type (0.15W), No- standard type (0.2W) 线圈功率: 无-标准型 (0.2W), L-灵敏型 (0.15W)
3. Coil Voltage 线圈规格 (VDC): DC3V,DC5V,DC6V,DC9V,DC12V,DC24V	6. Customer Special Code :XXX- Customer Special Requirements No - Standard Type 客户特性号: XXX-客户特殊要求, 无-标准型

TYPICAL USE 典型用途


- Automatic control, Communication equipment, Modem, Computer peripherals, Etc.
- 自动控制, 通讯设备, 调制解调器、电脑周边设备等。

SAFETY STANDARD 安规认证


AuthType Basic 认证类别	CQC	UL/C_UL
Authentication Load 认证负载	3A 125VAC	3A 125VAC 3A 30VDC




OUTLINE DIMENSIONS (UNIT:mm)外形尺寸 (单位: mm)




Dimensions尺寸



Dimensions尺寸



Wiring diagram (bottom view)
接线图 (底视图)




Mounting hole size (bottom view)
安装孔尺寸 (底视图)

Undimensioned tolerance: <1mm: ±0.2mm 1~5mm: ±0.3mm >5mm: ±0.4mm
未标注尺寸公差: <1mm: ±0.2mm 1~5mm: ±0.3mm >5mm: ±0.4mm

Note: 1. The size of the lead foot is pre welding dimension. 注: 1、引出脚尺寸为预焊前尺寸
2. installation hole size tolerance: +0.1mm 2、安装孔尺寸公差: ±0.1mm


PERFORMANCE CHART性能曲线图

Max. Switching Power
最大切换功率 (W)



Contact Voltage (V)
触点电压 (V)

Life Curve
寿命曲线



Contact Current (A)
触点电流 (A)