






RoHS



RECOMMENDED PCB LAYOUT
GENERAY TOLERANCE ± 0.05



SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出



Specifications/技术规格:

- 1.Current rating/额定电流: 0.5A
- 2.Voltage rating/额定电压: 125V AC/DC
- 3.Insulation Resistance/绝缘电阻: 100M Ω Min
- 4.Dielectric Withstanding/ 耐电压: 500V AC/minute
- 5.Contact Resistance/ 接触电阻: 100m Ω Max
- 6.Durability/ 耐久性: 5,000 Insertions
- 7.Operating Temperature/ 工作温度: -40 $^{\circ}$ C to +85 $^{\circ}$ C

①	Terminal		6	Phosphor bronze	Au plated
②	Contact		6	Phosphor bronze	Au plated
③	Cover		1	SUS	Ni Plating
④	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd


design	date	name	NANO SIM CARD CONNECTOR
Review	date	model	NANO-SIM-501A
Approved	date		

Drawing number: A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gaps number

RoHS

User Direction of Unreeling
User Direction of Unreeling



COVER TAPE PEELING ANGLE:165°~180°
PEELING FORCE:20~130g

CARRIER TAPE


User Direction of Unreeling

DETAIL B


DETAIL B

NOTES



1. NUMBER OF CONNECTORS:1800PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY:18000PCS/CARTON



TAPE ON



YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	NANO SIM CARD CONNECTOR
Review	date	model	NANO-SIM-501A
Approved	date		

Drawing number: Proportion 1:1 unit mm gape number A4

modify Review Approved

Tolerance not specified