

160101-9 ✓ ACTIVE


TE Internal #: 160101-9

Closed Ring Tongue Terminal, 20 – 16 AWG, M4 / #8 Stud Size, 4.3 mm [.169 in] Stud Diameter, Open Barrel, Straight, Nickel, Uninsulated

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **1021 – 2582 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.628 g
----------------	--------

Contact Features

Contact Base Material	Steel
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Nickel
Contact Underplating Material	None



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.08 in
Wire Size	1021 – 2582 CMA
Stud Diameter	4.3 mm [.169 in]
Tongue Thickness	.76 mm [.03 in]
Product Length	19.81 mm [.78 in]
Barrel Inside Diameter	1.65 mm, 2.28 mm [.065 in] [.09 in]
Compatible Insulation Diameter (Max)	3.05 mm [.12 in]
Compatible Insulation Diameter Range	2.03 – 3.04 mm [.08 – .12 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C [-40 – 482 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2150304-1
OCEAN_2.0_Applicator-E-110F140F-REM



KIT
REPRESENTATION ONLY

TE Part # 7-2150304-7
OCEAN_2.0_SPARE_PART_KIT-110F140F



TE Part # 1742775-1
RT .129 DIA TERMINAL .062 CABLE ST



TE Part # 1742777-1
RT .262 DIA TERMINAL .062 CABLE ST



TE Part # 2150304-2
OCEAN_2.0_Applicator-E-110F140F-REA

Customers Also Bought



TE Part #2273007-1
M8 x 1.0 straight socket Pigtail Shld



TE Part #170265-2
PL 250 REC 12-10 AWG 0.406 X 42.3



TE Part #927231-7
UMNL 9 WAY CAP HOUSING




TE Part #1-1863003-2
UMNL 9WAY PLUG HOUSING



TE Part #172520-6
6P 2.5MM MINI AMP-IN HDR HSG



TE Part #154718-6
250 PL MKI REC. 18-14AWG PTPB



TE Part #316185-002
55A1121-20-0/9-9



TE Part #2162663003
55A0111-26-5



TE Part #NB11014001
ATUM-4/1-0-SP



TE Part #254168-E
MICROS STV 12 9999 188 * 0007 J 3
254168

Documents

Product Drawings

[RING TONGUE 20-16 AWG 0.0253 NPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_160101-9_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160101-9_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_160101-9_Y.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English