



TE Internal #: 2071509-1

Power Relays, General Purpose Power Relay, Monostable, 450 mW

Coil Power Rating DC, 1280 Ω Coil Resistance, UL Coil Insulation Class F

[View on TE.com >](#)

Relays & Contactors > Relays > Power Relays



Relay Type: **General Purpose Power Relay**

Coil Magnetic System: **Monostable**

Coil Power Rating DC: **450 mW**

Coil Resistance: **1280 Ω**

Coil Special Features: **UL Coil Insulation Class F**

Features

Product Type Features

Relay Type	General Purpose Power Relay
------------	-----------------------------

Configuration Features

Coil Special Features	UL Coil Insulation Class F
Contact Arrangement	1 Form A (NO)
Contact Number of Poles	1

Electrical Characteristics

Contact Limiting Short-Time Current	10 A
Contact Limiting Continuous Current	10 A
Insulation Initial Dielectric Between Open Contacts	750 Vrms
Contact Limiting Making Current	10 A
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms
Contact Limiting Breaking Current	10 A
Coil Power Rating DC	450 mW
Coil Resistance	1280 Ω
Coil Voltage Rating	24 VDC
Contact Current Rating	10 A
Contact Switching Voltage (Max)	250 VAC
Contact Voltage Rating	250 VAC



Body Features

Primary Product Color	Black
Product Weight	6.5 g

Contact Features

Contact Material	AgSnO
------------------	-------

Termination Features

Relay Connection Type	PCB Termination
Terminal Configuration	Solder Pins

Mechanical Attachment

Product Mount Type	Printed Circuit Board
--------------------	-----------------------

Dimensions

Insulation Creepage Between Contact & Coil	9.4 mm
Product Width	10.2 mm[.401 in]
Product Length	18.2 mm[.716 in]
Product Height	15.2 mm[.598 in]

Usage Conditions

Environmental Category of Protection	RTII
Environmental Ambient Temperature (Max)	85 °C
Operating Temperature Range	-30 – 85 °C

Operation/Application

Actuating System	DC
Coil Magnetic System	Monostable

Packaging Features


Packaging Method	Box & Tray
------------------	------------

Other

Insulation Creepage Class	5.5 – 8 mm
Coil Power Rating Class	400 – 500 mW
Contact Current Class	5 – 10 A

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-OE4-OJ1
STD OEG Miniature PCB OJ/OJE Pow Relays



TE Part # 2071507-1
OJT-SS-112HM,00000



TE Part # 2071508-1
OJT-SS-105HM,00000

Customers Also Bought



TE Part #86016-2
MOD IV RECP LP




TE Part #5557969-1
MJ,TE,8P/8C,SHLD,PNL STOPS&G



TE Part #1-292230-8
1.5 MINI CT SGL V SMT W/BOSS 1



TE Part #2213189-3
Assembly, IPI Connector 22-18GA w cap



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2071509-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2071509-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2071509-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

OJT_TV-8_Rated_Relay_Flyer

English

OJT Series Relay Datasheet

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English

