



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Panel, Wire-to-Wire**

Number of Positions: **20**

Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	20
Number of Power Positions	0
Number of Signal Positions	20
Number of Rows	5

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
----------------	--------



Contact Current Rating (Max)	9 A
Contact Retention Within Housing	With
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	With
Mating Alignment	With
Panel Mount Feature	Without
Mating Retention Type	Positive Lock
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Color	Black
Housing Material	PA 66

Dimensions

Panel Thickness (Recommended)	1.73 mm[.068 in]
Connector Height	12.95 mm[.51 in]
Product Width	29.72 mm[1.17 in]
Product Length	21.34 mm[.84 in]
Compatible Insulation Diameter Range	2.92 mm[.115 in]
Wire Size	.12 – .8 mm²
Row-to-Row Spacing	4.19 mm[.165 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	LR 7189
UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL



Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	600
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2063388-1
TOOL, EXTRACTION



TE Part # 1-640514-0
20P MR II CAP HSG V0




TE Part # 2-640504-4
20P MR HDR ASSY VO LF



TE Part # 1-480634-9
20P STR/REL HNGD BLK



TE Part # 640504-1
20P MR HDR ASSY V0



TE Part # 640504-3
20P MR HDR ASSY V0



TE Part # 2-640504-2
20P MR HDR ASSY VO LF



TE Part # 640504-4
20P MR HDR ASSY V0

Also in the Series | AMP MR



Board-to-Board Jumpers & Shunts(4)



Power Cable Assemblies(1)



Rectangular Power Connectors(12)




Wire-to-Board Connector Assemblies & Housings(4)


Customers Also Bought



TE Part #3-644042-2
02P MTA100 CONN ASSY LF



TE Part #1-640521-0
09P MR II PLUG HSG V0




TE Part #1-640515-0
24P MR II CAP HSG V0



TE Part #1-640719-1
02P UMNL STR/REL NATL



TE Part #962834-1
FF 374 REC 2.5-4 MM2 PLAIN CUSN4



TE Part #640501-1
09P MR HDR ASSY V0



TE Part #1SNA238051R0400
RC1010 1->8 (X10) VERTICAL



TE Part #544720-E
SRCBUG A 2,54 2 2 CSI 163 * K-AD B500 J



TE Part #5070062068
[RNF-100-1/4-CL-STK](#)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-640524-0_AF.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640524-0_AF.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-640524-0_AF.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_1-640524-0_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_1-640524-0_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-640524-0_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English



AMP* MINIATURE RECTANGULAR II (MRII) CONNECTORS

English

Agency Approvals

Agency Approval Document

English