



PIDG

TE Internal #: 327583
Splices, Butt Splice, 16 – 14 AWG / 22 – 18 AWG Wire Size, 1.04 – 2.62 mm² / .26 – .96 mm² Wire Size, Serrated, Copper, Blue - Translucent, PIDG

[View on TE.com >](#)

Terminals & Splices > Splices > PIDG Stepdown Butt Splices



Splice Type: **Butt Splice**
Wire Size: .26 – .96 mm², 1.04 – 2.62 mm²
Sealable: **No**
Splice Features: **Serrated**

[All PIDG Stepdown Butt Splices \(6\)](#)

Features

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Serrations	8
Compatible With Wire & Cable Type	Discrete Wire

Electrical Characteristics

Operating Voltage	300 V
-------------------	-------

Body Features

Insulation Material	Nylon
Splice Features	Serrated



Primary Product Color	Blue - Transluscent
-----------------------	---------------------

Contact Features

Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Recovered Inside Diameter	3.89 mm[.153 in]
Wire Size	.26 – .96 mm², 1.04 – 2.62 mm²
Terminal Material Thickness	.46 mm[.018 in]
Product Length	32.13 mm[1.265 in]

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	105 °C[221 °F]

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free





Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 58433-3 PRO CR ASSY, RBY IS9252	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY	 TE Part # 58423-1 DIE, RBY IS9252
 TE Part # 47387-7 DAHT PG PIDG 16-12 ASSY	 TE Part # 47386 DAHT PG PIDG 26-16 ASSY	 TE Part # 47387 DAHT PG PIDG 20-14 ASSY	 TE Part # 525691 DAHT PG PIDG 16-14 ASSY
 TE Part # 539691-2 ERGO DIE R.B.Y	 TE Part # 1-47387-0 DAHT PIDG PG 16-14 HEAD	 TE Part # 2063030-1 SDE DIESET, RBY, UL	 TE Part # 47807-1 DIES PIDG 16-14 DIE SET



TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 2392022-2
BLUE BATTERY DAHT KIT 220V (47387-7)

TE Part # 2392022-1
BLUE BATTERY DAHT KIT 110V (47387-7)

TE Part # 169404
CERTI-LOK DIE

TE Part # 1SET191001R0000
CRIMP-HT

TE Part # 1SET191002R0000
TET CRIMP-HT

Also in the Series | PIDG

Compression Connectors(17)

Crimp Wire Pins, Tabs & Ferrules(41)

Hand Crimping Tools(2)

Knife Disconnects(11)

Quick Disconnects(32)

Ring Terminals(589)

Spade Terminals(228)

Special Purpose Terminals(1)

Splices(40)

Customers Also Bought



TE Part #787610-1
CPC RECPT, SIZE 23-37 W/INSERTS

TE Part #4-1879074-2
THS15 5K6 5%

TE Part #66100-9
III+ SKT, 18-16, 30AU/FL, STRIP

TE Part #1445807-1
PLUG, 11-9, SM INS, STD KEY

TE Part #1586024-5
5P S/R FH PLUG VAL-U-LOK V2

TE Part #4-192041-1
LA4(.006)GOLD

TE Part #D369-R99-NP0
369 9 WAY REC, NO CONTACTS, PIN

TE Part #CB5085-000
HF-07FRX25

TE Part #4-1393159-8
20C318=SPRING, HOLD-DOWN, K10, 0

Documents

Product Drawings

SPLICE BUTT PIDG 16-14/22-18

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_327583_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_327583_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_327583_H.3d_stp.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_327583_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_327583_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_327583_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[PIDG TERMINALS & SPLICES Quick Reference Guide](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English