Description：

This N-Channel MOSFET uses advanced trench technology and design to provide excellent $R_{DS(on)}$ with low gate charge.

It can be used in a wide variety of applications.



TO-252

Features：

1) V_{DS}=60V,I_D=20A,$R_{DS(ON)}$<36mΩ @V_{GS}=10V
2) Low gate charge.
3) Green device available.
4) Advanced high cell denity trench technology for ultra $R_{DS(ON)}$.
5) Excellent package for good heat dissipation.



JSMICRO Semiconductor

Absolute Maximum Ratings：(T_C=25℃ unless otherwise noted)

Symbol	Parameter	Ratings	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	±20	V
I_D	Continuous Drain Current-T_C=25℃	20	A
	Continuous Drain Current-T_C=100℃	13	
I_{DM}	Pulsed Drain Current note1	80	
E_{AS}	Single Pulse Avalanche Energy note2	40	mJ
P_D	Power Dissipation,T_C=25℃	31	W
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	℃

Thermal Characteristics：

Symbol	Parameter	Max	Units
$R_{\theta JC}$	Thermal Resistance,Junction to Case	4	℃/W

Electrical Characteristics: (T_C=25℃ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain-Sourtce Breakdown Voltage	V_{GS}=0V,I_D=250μA	60	---	---	V
I_{DSS}	Zero Gate Voltage Drain Current	V_{GS}=0V, V_{DS}=60V	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V, V_{DS}=0A	---	---	±100	nA
On Characteristics						
$V_{GS(th)}$	GATE-Source Threshold Voltage	V_{GS}=V_{DS}, I_D=250μA	1	1.6	3	V
$R_{DS(on)}$	Drain-Source On Resistance note3	V_{GS}=10V,I_D=10A	---	26	36	mΩ
		V_{GS}=4.5V,I_D=5A	---	36	45	mΩ
Dynamic Characteristics						
C_{iss}	Input Capacitance	V_{DS}=25V, V_{GS}=0V, f=1MHz	---	1150	---	pF
C_{oss}	Output Capacitance		---	55	---	
C_{rss}	Reverse Transfer Capacitance		---	45.3	---	
Switching Characteristics						
$t_{d(on)}$	Turn-On Delay Time	V_{DS}=30V, I_D=15A, V_{GS}=10V,R_{GEN}=1.8Ω	---	7.6	---	ns
t_r	Rise Time		---	20	---	ns
$t_{d(off)}$	Turn-Off Delay Time		---	15	---	ns
t_f	Fall Time		---	24	---	ns
Q_g	Total Gate Charge	V_{GS}=10V, V_{DS}=30V, I_D=10A	---	20.3	---	nC
Q_{gs}	Gate-Source Charge		---	3.7	---	nC
Q_{gd}	Gate-Drain “Miller” Charge		---	5.3	---	nC
Drain-Source Diode Characteristics						
V_{SD}	Source-Drain Diode Forward Voltage	V_{GS}=0V,I_S=20A	---	---	1.2	V
Is	Maximum Continuous Drain to Source Diode Forward Current		---	---	20	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current		---	---	80	A

JSMICRO Semiconductor

trr	Reverse Recovery Time	IF =10A，di/dt = 100A/μs	---	29	---	Ns
qrr	Reverse Recovery Charge		---	43	---	nc

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : T_J=25℃,V_{DD}=30V,V_G=10V,L=0.5mH,Rg=25Ω
3. Pulse Test: Pulse Width≤300μs, Duty Cycle≤0.5%

Typical Characteristics：

(T_C=25℃ unless otherwise noted)



Figure 1 Output Characteristics



Figure 2 Transfer Characteristics



Figure 3 Rdson- Drain Current



Figure 4 Rdson-Junction Temperature

JSMICRO semiconductor



Fiure 5 Gate Chare



Figure 6 Source- Drain Diode Forward



Figure 7 Capacitance vs Vds



Figure 8 Safe Operation Area



Fi ure 9 BV vs Junction Temerature



Figure 10 $V_{GS(th)}$ vs Junction Temperature

JSMICRO Semiconductor



Figure 11 Normalized Maximum Transient Thermal Impedance

JSMICRO Semiconductor

Package Information

TO-252





Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	6.30	6.90	0.248	0.272
A1	0.00	0.16	0.000	0.006
B	5.70	6.30	0.224	0.248
C	2.10	2.50	0.083	0.098
D	0.30	0.70	0.012	0.028
E1	0.60	0.90	0.024	0.035
E2	0.70	1.00	0.028	0.039
F	0.30	0.60	0.012	0.024
G	0.70	1.20	0.028	0.047
L1	9.60	10.50	0.378	0.413
L2	2.70	3.10	0.106	0.122
H	0.40	1.00	0.016	0.039
M	5.10	5.50	0.201	0.217
N	2.09	2.49	0.082	0.098
R	0.30		0.012	
T	1.40	1.60	0.055	0.063
Y	5.10	6.30	0.201	0.248

JSMICRO Semiconductor