



Part Number : 1200651133

Series Number : 120065

Product Category : Circular Industrial Cordsets

Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 10.0m (32.81') Length

Status : Active

Engineering Number : 804006K05M100

Documents & Resources

Drawings

Drawing 1200651133_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120065
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, Yellow TPE Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Protocol	N/A
Region	America
Type	Single Ended
UPC	78678885459

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.30mm (.209")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No

Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	488.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	22

This document was generated on Jul 18, 2024