




Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
Magnet Wire Size: **.16 – 1.02 mm**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention Type	Barbs, Dimple
-----------------------	---------------

Dimensions

Terminal Height	8.38 mm[.33 in]
Magnet Wire Size	.16 – 1.02 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]



Product Length20.45 mm[.805 in]

Usage Conditions

Insulation OptionUninsulated

Operation/Application

Compatible With Wire Base MaterialCopper

Packaging Features

Packaging MethodReel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1601061-2
TAB,250X032,STD,SMZ

TE Part # 3-1601061-2
TAB,250X032,STD,SMZ

TE Part # 2-284937-1
TAB SIAMEZE CONTACT .250" x.03

TE Part # 2348504-2
STD RANGE WIRE TO .250 X .032 TAB
SMZ

TE Part # 293214-1
1.5 SIAMEZE TAB CTC. FOR RAST 2,5
APPL.

TE Part # 1601425
531-007-000=POCKET
SPECIFICATION

Also in the Series

SIAMEZE

Insertion & Extraction Tools(1)

Magnet Wire Terminals(192)

Customers Also Bought

TE Part #104257-1
02 MTE RCPT HSG SR LATCH .100

TE Part #794896-1
2 CIR MINI UMNL RND WIRE HOLES

TE Part #1-770903-0
MINI UMNL PIN 22-18 AWG AU

TE Part #794758-1
MINI UMNL WIRE SEAL,18-26AWG

TE Part #1-104480-3
SHORT POINT CONT 30 DPLX
STMPD LF

TE Part #4-1601041-3
PC TAB STANDARD SIAMEZE

TE Part #1-1601061-2
TAB,250X032,STD,SMZ

TE Part #3-1601061-2
TAB,250X032,STD,SMZ



Documents

Product Drawings

[131-128-002=TAB,250X032,STDSMZ](#)

English

[131-128-002=TAB,250X032,STDSMZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1601061-2_G_c-2-1601061-2-g.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1601061-2_G_c-2-1601061-2-g.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1601061-2_G_c-2-1601061-2-g.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

[Magnet Wire Terminals & Splices](#)

English

[1-1773702-7 _IDC_Magnet_Wire](#)

English

Product Specifications

[Application Specification](#)

English