

Specification Sheet

Part Number: 170-03161



Self extinguishing material does not melt and is unaffected by most acids, and provides excellent thermal stability against direct flame.
Provides excellent thermal stability.
Meets FMVSS 302 specifications for use in automotive engineering.
Material cuts with ordinary scissors which reduces assembly time.

Nomex® High Temperature Woven Sleeve, 0.5" Dia, Green, 100 ft/bulk reel

Article Number	170-03161
Type	BSNMX125B
Color	Green (GN)
Quantity Per	reel
Product Description	A densely woven aramid fiber sleeve, this soft and flexible material is self extinguishing and can withstand temperatures reaching up to 662°F.
Short Description	Nomex® High Temperature Woven Sleeve, 0.5" Dia, Green, 100 ft/bulk reel
Global Part Name	BSNMX125B-PMPI-GN

Length L (Imperial) 100.0

Length L (Metric) 30.48

Bundle Diameter Min (Imperial) 0.31

Bundle Diameter Min (Metric) 7.9

Bundle Diameter Max (Imperial) 0.63

Bundle Diameter Max (Metric) 16.0

Diameter D (Imperial) 0.50

Diameter D (Metric) 12.7

Nominal Diameter (Imperial) 0.5

Nominal Diameter (Metric) 12.7

Material Polyaramid Polymetaphenylene Isophthalamide (PMPI)

Material Shortcut PMPI

Flammability UL VW-1

Halogen Free Yes

UV Resistant (Yes/No) No

Operating Temperature	-320°F to +662°F (-196 °C to +350 °C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	5806322000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).