




Glass Passivated Rectifier Diode Modules

VRRM 2000V
IFAV 240 A

Applications

- Non-controllable rectifiers for AC/AC converters
- Line rectifiers for transistorized AC motor controllers
- Field supply for DC motors



Features

- Blocking voltage:2000V
- Heat transfer through aluminum oxide ceramic isolated metal baseplate
- Glass passivated chip

Module Type

TYPE	VRRM	VRSM
MD240C20D2	2000V	2100V

Maximum Ratings

Symbol	Conditions	Values	Units
IFAV	Single phase ,half wave 180° conduction Tc=95°C	240	A
IFSM	t=10mS Tvj =45°C	10800	A
i ² t	t=10mS Tvj =45°C	583200	A ² s
Visol	a.c.50HZ;r.m.s.;1min	3000	V
Tvj		-40 to 150	°C
Tstg		-40 to 125	°C
Mt	To terminals(M6)	5±15%	Nm
Ms	To heat sink(M6)	5±15%	Nm
Weight	Module (Approximately)	160	g

Thermal Characteristics

Symbol	Conditions	Values	Units
Rth(j-c)	Per diode	0.16	°C/W
Rth(j-c)	Per module	0.08	°C/W
Rth(c-s)	Module	0.05	°C/W



Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
V _{FM}	T=25°C I _F =300A	—	1.15	1.25	V
I _{RD}	T _{vj} =150°C V _{RD} =V _{RRM}	—	—	9	mA
r _F	T _J =25°C	-	1.16	-	mΩ
	T _J =150°C	-	1.17	-	mΩ
V _{FO}	T _J =25°C	-	0.79	-	V
	T _J =150°C	-	0.67	-	V

Performance Curves




Fig1. Power dissipation




Fig2. Forward Current Derating Curve




Fig3. Transient thermal impedance




Fig4. Max Non-Repetitive Forward Surge Current




Fig5. Forward Characteristics

Package Outline Information

