



Product Summary

- $V_{DS} = -20V, I_D = -4.1A$
- $R_{DS(ON)} < 75m\Omega @ V_{GS} = -2.5V$
- $R_{DS(ON)} < 52m\Omega @ V_{GS} = -4.5V$
- Advanced Trench Technology
- Excellent $R_{DS(ON)}$ and Low Gate Charge
- Lead free product is acquired

Application


- Load/Power Switching
- Interfacing Switching
- Logic Level Shift

Package and Pin Configuration

SOT-23



Circuit diagram



Marking:



Absolute Maximum Ratings ($T_A = 25^\circ C$ unless otherwise noted)

| Parameter | Symbol | Limit | Unit |
|--|----------------|------------|------|
| Drain-Source Voltage | V_{DS} | -20 | V |
| Gate-Source Voltage | V_{GS} | ± 12 | V |
| Continuous Drain Current | I_D | -4.1 | A |
| | | -3.2 | |
| | | -3 | |
| | | -2.3 | |
| Drain Current -Pulsed (Note 1) | I_{DM} | -15 | A |
| Maximum Power Dissipation | P_D | 1.7 | W |
| Operating Junction and Storage Temperature Range | T_J, T_{STG} | -55 To 150 | °C |

Thermal Characteristic

| | | | |
|---|-----------------|----|------|
| Thermal Resistance,Junction-to-Ambient (Note 2) | $R_{\theta JA}$ | 74 | °C/W |
|---|-----------------|----|------|



Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Condition | Min | Typ | Max | Unit |
|---|--------------------------|--|-------|------|-----------|------------------|
| Off Characteristics | | | | | | |
| Drain-Source Breakdown Voltage | BV_{DSS} | $V_{\text{GS}}=0\text{V}, I_{\text{D}}=-250\mu\text{A}$ | -20 | - | - | V |
| Zero Gate Voltage Drain Current | I_{DSS} | $V_{\text{DS}}=-20\text{V}, V_{\text{GS}}=0\text{V}$ | - | - | -1 | μA |
| Gate-Body Leakage Current | I_{GSS} | $V_{\text{GS}}=\pm 12\text{V}, V_{\text{DS}}=0\text{V}$ | - | - | ± 100 | nA |
| On Characteristics (Note 3) | | | | | | |
| Gate Threshold Voltage | $V_{\text{GS(th)}}$ | $V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=-250\mu\text{A}$ | -0.45 | -0.7 | -1.0 | V |
| Drain-Source On-State Resistance | $R_{\text{DS(ON)}}$ | $V_{\text{GS}}=-4.5\text{V}, I_{\text{D}}=-4.1\text{A}$ | - | 45 | 55 | $\text{m}\Omega$ |
| | | $V_{\text{GS}}=-2.5\text{V}, I_{\text{D}}=-3\text{A}$ | - | 58 | 75 | |
| Forward Transconductance | g_{fs} | $V_{\text{DS}}=-5\text{V}, I_{\text{D}}=-2\text{A}$ | 6 | - | - | S |
| Dynamic Characteristics (Note 4) | | | | | | |
| Input Capacitance | C_{iss} | $V_{\text{DS}}=-4\text{V}, V_{\text{GS}}=0\text{V}, F=1.0\text{MHz}$ | - | 740 | - | PF |
| Output Capacitance | C_{oss} | | - | 290 | - | PF |
| Reverse Transfer Capacitance | C_{rss} | | - | 190 | - | PF |
| Switching Characteristics (Note 4) | | | | | | |
| Turn-on Delay Time | $t_{\text{d(on)}}$ | $V_{\text{DD}}=-4\text{V}, I_{\text{D}}=-3.3\text{A}, R_{\text{L}}=1.2\Omega, V_{\text{GEN}}=-4.5\text{V}, R_{\text{g}}=1\Omega$ | - | 12 | - | nS |
| Turn-on Rise Time | t_{r} | | - | 35 | - | nS |
| Turn-Off Delay Time | $t_{\text{d(off)}}$ | | - | 30 | - | nS |
| Turn-Off Fall Time | t_{f} | | - | 10 | - | nS |
| Total Gate Charge | Q_{g} | $V_{\text{DS}}=-4\text{V}, I_{\text{D}}=-4.1\text{A}, V_{\text{GS}}=-4.5\text{V}$ | - | 7.8 | - | nC |
| Gate-Source Charge | Q_{gs} | | - | 1.2 | - | nC |
| Gate-Drain Charge | Q_{gd} | | - | 1.6 | - | nC |
| Drain-Source Diode Characteristics | | | | | | |
| Diode Forward Voltage (Note 3) | V_{SD} | $V_{\text{GS}}=0\text{V}, I_{\text{S}}=-1.6\text{A}$ | - | - | -1.2 | V |
| Diode Forward Current (Note 2) | I_{S} | | - | - | 1.6 | A |

Typical Electrical and Thermal Characteristics




Figure 1:Switching Test Circuit






Figure 2:Switching Waveforms




T_j-Junction Temperature(°C)

Figure 3 Power Dissipation




T_j-Junction Temperature(°C)

Figure 4 Drain Current



V_{DS} Drain-Source Voltage (V)

Figure 5 Output Characteristics



I_D - Drain Current (A)

Figure 6 Drain-Source On-Resistance




Figure 7 Transfer Characteristics




Figure 8 Drain-Source On-Resistance




Figure 9 $R_{DS(on)}$ vs V_{GS}




Figure 10 Capacitance vs V_{DS}




Figure 11 Gate Charge




Figure 12 Source-Drain Diode Forward




Figure 13 Safe Operation Area





Figure 14 Normalized Maximum Transient Thermal Impedance

SOT-23 Package Information


| Symbol | Dimensions in Millimeters | |
|---------------|----------------------------------|-------------|
| | MIN. | MAX. |
| A | 0.900 | 1.150 |
| A1 | 0.000 | 0.100 |
| A2 | 0.900 | 1.050 |
| b | 0.300 | 0.500 |
| c | 0.080 | 0.150 |
| D | 2.800 | 3.000 |
| E | 1.200 | 1.400 |
| E1 | 2.250 | 2.550 |
| e | 0.950TYP | |
| e1 | 1.800 | 2.000 |
| L | 0.550REF | |
| L1 | 0.300 | 0.500 |
| θ | 0° | 8° |