



Glass Passivated Rectifier Diode Modules


VRRM 800 to 1800V
IFAV 300 A

Applications

- Non-controllable rectifiers for AC/AC converters
- Line rectifiers for transistorized AC motor controllers
- Field supply for DC motors

Features

- Blocking voltage: 800 to 1800V
- Heat transfer through aluminum oxide ceramic isolated metal baseplate
- Glass passivated chip



Module Type

TYPE	VRRM	VRSM
MD300U08D2	800V	900V
MD300U12D2	1200V	1300V
MD300U16D2	1600V	1700V
MD300U18D2	1800V	1900V

Maximum Ratings

Symbol	Conditions	Values	Units
IFAV	Single phase ,half wave 180° conduction Tc=95℃	300	A
IFSM	t=10mS Tvj =45℃	9000	A
i ² t	t=10mS Tvj =45℃	405000	A ² s
V _{isol}	a.c.50HZ;r.m.s.;1min	3000	V
Tvj		-40 to 150	℃
T _{stg}		-40 to 125	℃
Mt	To terminals(M6)	5±15%	Nm
Ms	To heatsink(M6)	5±15%	Nm
Weight	Module (Approximately)	160	g

Thermal Characteristics

Symbol	Conditions	Values	Units
R _{th(j-c)}	Per Module	0.09	℃/W
R _{th(c-s)}	Module	0.05	℃/W

Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
V _{FM}	T=25℃ IF =300A	—	1.18	1.30	V
I _{RD}	Tvj=150℃ VRD=VRRM	—	—	5	mA
r _f	Tj=25℃		1.13		mΩ
V _{f0}			0.84		V

Performance Curves




Fig1. Power dissipation




Fig2. Forward Current Derating Curve




Fig3. Transient thermal impedance




Fig4. Max Non-Repetitive Forward Surge Current





Fig5. Forward Characteristics

Package Outline Information

CASE: D2



Dimensions in mm