



LOCTITE® M - 18

August 2012

PRODUCT DESCRIPTION

LOCTITE® M - 18 is a rust prohibit and lubricant for use on metal or plastic parts. It also can be used as cleaner, penetrant and moisture displayer.

PRODUCT APPLICATIONS

- Automotive
- Bicycle / Motorcycle
- Furniture
- Electro-mechanical assemblies

PHYSICAL PROPERTIES

- Appearance: Clear or light yellow liquid
- Odor: Aromatic
- Specific Gravity: 0.80 (base only)
- Vapor Pressure: 6.4 kg/cm² (0.65 Mpa)

BENEFITS

- Powerful penetration
- Long term rust protection
- Strong lubricator
- Surface cleaner
- No CFC's

DIRECTIONS TO USE

1. Shake can well.
2. Raise steel straw and spray from 5-10 cm distance.
3. For very tight parts, spray 2 - 3 times and apply extra force to loosen.

CAUTIONS

- Keep away from fire or high heat.
- Provide adequate ventilation.
- Completely evacuate container before disposal.
- Keep out of reach of children.
- Please read and follow the directions on the product label.

CAN SPECIFICATION

- Type: 211 - dia, Necked in can
- Size: Vol. 360 ml
- Material: Tin plate
- Can height (mm): 121.0
- Total height (mm): 139.8
- Dip tube (mm): 125
- Valve: PV - 244W
- Actuator: 2 - way cap (Steel straw)

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

STORAGE

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling. **Optimal Storage: 4 °C to 40 °C. Storage below 4 °C or greater than 40 °C can adversely affect product properties.**

Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those recommended. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Note

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 1.3