



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 33100 – 52600 CMA

Stud Size: 1/4, M6

Features

Product Type Features

|                                        |                             |
|----------------------------------------|-----------------------------|
| Ring Terminal Product Type             | Closed Ring Tongue Terminal |
| Stud Size                              | 1/4, M6                     |
| Sealable                               | No                          |
| Wire Insulation Support Retention Type | Non-Insulation Support      |

Configuration Features

|                 |   |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

Contact Features

|                           |          |
|---------------------------|----------|
| Barrel Type               | Closed   |
| Terminal Orientation      | Straight |
| Terminal Plating Material | Tin      |

Mechanical Attachment

|                         |         |
|-------------------------|---------|
| Wire Insulation Support | Without |
|-------------------------|---------|

Dimensions

|                  |                   |
|------------------|-------------------|
| Wire Size        | 33100 – 52600 CMA |
| Stud Diameter    | 6.73 mm[.265 in]  |
| Tongue Thickness | 1.78 mm[.07 in]   |

|                        |                    |
|------------------------|--------------------|
| Product Length         | 33.38 mm[1.314 in] |
| Barrel Inside Diameter | 7.52 mm[.296 in]   |

Usage Conditions

|                             |                |
|-----------------------------|----------------|
| Insulation Option           | Uninsulated    |
| Operating Temperature Range | 170 °C[338 °F] |

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 100         |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2024 (240)<br>Candidate List Declared Against: JAN 2024 (240)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                    |                                                                                                                                           |                                                                                                                                             |                                                                                                                                          |
|----------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 601075<br/>BANTAM ROTA-CRIMP TOOL</p>               |  <p>TE Part # 2-33469-4<br/>TERMINAL,SOLIS R 4 1/4</p>   |  <p>TE Part # 8-33469-2<br/>TERMINAL,SOLIS R 4 1/4</p>   |  <p>TE Part # 1490413-3<br/>HYP10 SOLIS 4AWG NEST</p> |
|  <p>TE Part # 1490414-2<br/>HYP10 SOLIS HD 6-4AWG INDENTER</p>  |  <p>TE Part # 48127<br/>HYP8 SOLIS 6-2AWG INDENTER</p> |  <p>TE Part # 69218<br/>HYP8/10 SOLIS 4AWG DIE SET</p> |  <p>TE Part # 600850<br/>ROTO-CRIMP TOOL (ASI)</p>  |
|  <p>TE Part # 1901000-2<br/>NEST #4</p>                         |  <p>TE Part # 1901002-1<br/>INDENTER, SOLISTRAND</p>   |  <p>TE Part # 48129<br/>HYP8 SOLIS 4AWG NEST</p>       |  <p>TE Part # 2-1377172-6<br/>SMP 0-0033469-0</p>   |
|  <p>TE Part # 33469-1<br/>TERMINAL,SOLIS, R, 4, 1/4, UNPLTD</p> |                                                                                                                                           |                                                                                                                                             |                                                                                                                                          |

Customers Also Bought






TE Part #36917  
TERMINAL,SOLIS R 1/0 3/8




TE Part #323127  
SOLIS SPD 22-16COMM 22-18MIL 6



TE Part #1825096-1  
TPA11CGPC004



TE Part #8-1437652-3  
6PCV-05-008=#6TRIBARRIER TERMI



TE Part #4-1617076-6  
3SBH5004K5 = RELAY

TE Part #1520231-1  
7410K4=20 AMP TOGGLE FLUSH  
MOU

Documents

Product Drawings

TERMINAL,SOLIS R 4 1/4

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_33469\_AF.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_33469\_AF.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_33469\_AF.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_33469\_L.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_33469\_L.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_33469\_L.2d\_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOLISTRAND - QRG

English

Agency Approvals

UL Report

English

UL Report

English