

## Specification Sheet

Part Number: 2N0M



Sheathing allows flexible routing and lead-out of cables  
The inner edges are beveled preventing damage to cables  
Sheathing is reusable and resistant to most chemicals  
Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.25" Diameter, PA6, Black, 1000ft/roll

Article Number 161-05033

Type 2N

Color Black (BK)

Quantity Per reel

Product Description HellermannTyton Spiralwrap provides an effective means for routing and securing wires around corners and bends, and helps keep wires out of pinch points within moving panel doors. Spiralwrap is installed using a gapped or butted installation which impacts harnesses flexibility, wire coverage and abrasion resistance. A gapped installation leaves space between the sheathing to accommodate breakouts and adds flexibility to the harness. A butted installation wraps tightly around the bundle to provide greater abrasion resistance and add rigidity. Natural PA6 nylon material is recommended for use within enclosed environments where possibility of fire exists. Black PA6 nylon material is suitable for outdoor applications and can be used in direct sunlight for extended periods of time.

Short Description	Spiralwrap Protective Sheathing, 0.25" Diameter, PA6, Black, 1000ft/roll
Global Part Name	2N-PA6-BK
Length L (Imperial)	1000.0
Length L (Metric)	304.8
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.18
Bundle Diameter Min (Metric)	4.75
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.8
Diameter D (Imperial)	0.25
Diameter D (Metric)	5.1
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6.35
Wall Thickness WT (Imperial)	.025
Wall Thickness WT (Metric)	0.64

Material Polyamide 6 (PA6)

Material Shortcut PA6

Flammability UL 94 HB

UV Resistant (Yes/No) No

Operating Temperature -40°F to +250°F (-40°C to +121°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 304.8

Customs Number 3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)