




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FPC Connectors



Connector System: **Flex-to-Board**
Number of Positions: **8**
Centerline (Pitch): **1 mm [.039 in]**
Insertion Force Type: **Zero Insertion Force (ZIF)**
PCB Mount Orientation: **Right Angle**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector Product Type	Connector Assembly
Connector System	Flex-to-Board
Insertion Force Type	Zero Insertion Force (ZIF)
FPC Actuator Type	Stuffer (Plunger Style)
Connector & Contact Terminates To	Flexible Printed Circuit (FPC), Printed Circuit Board

Configuration Features

Compatible With Wire & Cable Type	FFC, FPC
Number of Rows	1
Number of Positions	8
PCB Mount Orientation	Right Angle

Electrical Characteristics

Operating Voltage	200 VAC
-------------------	---------

Body Features



Primary Product Color	Natural
-----------------------	---------

Contact Features

PCB Contact Termination Area Plating Material Thickness	.05 µm[2 µin]
Contact Layout	Inline
Contact Type	Socket
Contact Mating Area Plating Material Thickness	.05 µm[2 µin]
Contact Shape & Form	Standard Flat
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
Contact Mating Location	Bottom
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1 A

Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Board Mount
PCB Mount Alignment	Without
PCB Mount Retention	With

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	1 mm[.039 in]

Dimensions

Connector Length	15.92 mm[.627 in]
Connector Height	2.56 mm[.101 in]
Connector Width	5.4 mm[.213 in]
Accepts Flex Cable Thickness	.3 mm[.012 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------



Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Packaging Features

Packaging Quantity	1500
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 84982-8
1MM FFC SMT V ASSY 8P EMBOSS

TE Part # 487952-8
008 1MM FPC BTM HORZ

Customers Also Bought

TE Part #2-1437565-8
FSM2JSMMA=TACTILE 260G FORCE S

TE Part #3-84953-0
1MM FPC HORZ.TOP CONT.ASSY 30P

TE Part #2-84953-0
1MM FPC HORZ.TOP CONT.ASSY 20P

TE Part #284507-3
3 POS TERMI-BLOK PLUG STAC 3,8

TE Part #284507-4
4 POS TERMI-BLOK PLUG STAC 3,8

TE Part #284513-3
3 POS TERMI-BLOK HDR 900 POL.

TE Part #1624209-2
23SE 4K7A 6.35X50FL B7 CAT

TE Part #1571626-4
TACT,SMT,GULL WING,100GF,T&R

TE Part #2-2176327-3
CRGP 0805 680R 1%

TE Part #0081930001
ES-CAP-NO.1-C1-X-30MM

Documents

Product Drawings

1MM FPC HORZ.BOTTOM CONT.ASSY 8P (Au)

English

CAD Files

Customer View Model

ENG_CVM_1735265-8_B.3d_igs.zip

English

Customer View Model



[ENG_CVM_1735265-8_B.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1735265-8_B.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773959-7-FPC-Connectors-CN](#)

English

Product Specifications

Product Specification

English