



SECTION E-E
SCALE 2:1



BOARDLOCKS TYPE

TAB TYPE



广东星坤科技股份有限公司
文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δ					ANGLAR ±5°
Δ					L ≤ 4 ±0.2
Δ					4 < L ≤ 16 ±0.3
Δ					16 < L ≤ 63 ±0.4
Δ					L > 63 ±0.5
	REVISIONS				




DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X9413WVS-288XX-9TV15
CHKD	UNIT: mm/in	DWG NO.: X-X9413WVS-288XX-9TV15
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0

XKB INDUSTRIAL PRECISION CO., LIMITED



RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 BOARDLOCKS



RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 TABS

-Z-

广东星坤科技股份有限公司

Δ*	日期
Δ*	日期
Δ*	日期
MARK	DESCRIPTION
文件	工程章


					ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.:
CHKD	UNIT: mm/in	X9413WVS-288XX-9TV15
APPD	SIZE: A4	DWG NO.:
		X-X9413WVS-288XX-9TV15

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0



21.75	20.70	147.30	162.00	LONG
21.00	20.30	142.35	156.00	MIDDLE
20.50	20.20	140.80	152.00	SHORT
DIM.D	DIM.C	DIM.B±0.30	DIM.A	LATCH TYPE

X9413 W V S - 288 X X X -9T V15
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- 1.Series Nunber
- 2.Terminal form: W-Wafer
- 3.Welding Board Angle : V-Stright Angle 180°
- 4.Welding Way:S-SMT
- 5.No.of Pins: XX-288 Pin
- 6.Board Lock Type: B-Board Locks Type;T-TAB type
- 7.Latch Type: 1.short latch;2.long latch;3.middle Latch
- 8.Special No:M-With Mylar ; Blank-without Mylar
- 9.latchPlastic material: PA46 /PA9T UL94V-0
- 10.Contact Plating:V01-Gold Flash
 V15-Gold 15u"
 V30-Gold 30u"

NOTES 注释:

1. MATERIAL材料:

- 1.1 HOUSING外壳: HIGH PERFROMANCE RESINS, GLASS FILBER, UL94V-0;COLOR:SEE PART NO.
- 1.2 LATCH锁: HIGH PERFROMANCE RESINS, GLASS FILBER, UL94 V-O, COLOR: SEE PART NO.
- 1.3 CONTACTS触点: COPPER ALLOY.
- 1.4 BOARDLOCK针脚: STAINLESS STEEL.
- 1.5 TABS标签: STAINLESS STEEL.

2. FINISH饰面:

2.1 CONTACT触点:

- [SEE PART NO..] GOLD PLATING ON THE CONTACT AREA.
 2.54um [100u"] MIN. MATTE-TIN PLATING ON THE SOLDERING AREA
 1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

广东星坤科技股份有限公司

DATE	日期
REVISIONS	文件工程章

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X9413WVS-288XX-9TV15
CHKD	UNIT: mm/in	DWG NO.: X-X9413WVS-288XX-9TV15
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0
XKB INDUSTRIAL PRECISION CO., LIMITED		