

MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED

HT72XX-MS

Product specification

GENERAL DESCRIPTION

HT72XX-MS series are a set of Low Dropout Linear Regulator ICs implemented in CMOS technology. They can withstand voltage 10V. And they are available with low voltage drop and low quiescent current, widely used in audio, video and communication appliances.



FEATURES

- Low Power Consumption
- Low Voltage Drop
- Low Temperature Coefficient
- Withstanding Voltage 10V
- Quiescent Current 2.0 μ A
- Output Voltage Accuracy: tolerance $\pm 2\%$
- High output current: 300mA

TYPICAL APPLICATIONS

- Battery-powered Equipments
- Communication Equipments
- Audio/Video Equipments


PACKAGE/ORDER INFORMATION

Part Number	Output	Package		Pin Configuration	Marking	QTY
HT7228-MS	2.8V	SOT89-3				1000
HT7230-MS	3.0V					1000
HT7233-MS	3.3V					1000
HT7236-MS	3.6V					1000
HT7250-MS	5.0V					1000

PIN DESCRIPTION

Pin Number	Pin Name	Functions
1	V _{SS}	Ground
2	V _{IN}	Power Input
3	V _{OUT}	Output

FUNCTIONALBLOCKDIAGRAM



ABSOLUTE MAXIMUM RATINGS

Description	Symbol	Value range	Unit
Limit Power Voltage	V_{IN}	$-0.3 \sim +15$	V
Storage Temperature Range	T_{STG}	$-50 \sim +125$	$^{\circ}C$
Operating Free-air Temperature Range	T_A	$-40 \sim +85$	$^{\circ}C$

Note : Stresses greater than those listed under “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “Recommended Operating Conditions” is not implied. Exposure to “Absolute Maximum Ratings” for extended periods may affect device reliability.

HEAT DISSIPATION

Description	Symbol	Package	Value range	Unit
Thermal resistance	θ_{JA}	SOT89	200	$^{\circ}C/W$
Power dissipation	P_W	SOT89	500	mW

DC CHARACTERISTICS (unless otherwise noted $T_A = \pm 25^\circ\text{C}$)

 $(V_{IN} = V_{OUT} + 2\text{V}, V_{CE} = V_{IN}, C_{IN} = C_L = 10\mu\text{F}, T_a = 25^\circ\text{C}, \text{ unless otherwise noted})$

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Output Voltage	$V_{OUT(E)}$ (Note 2)	$I_{OUT} = 10\text{mA}$, $V_{IN} = V_{OUT} + 2\text{V}$	X 0.98	$V_{OUT(T)}$ (Note 1)	X 1.02	V
Maximum Output Current	I_{OUTMAX}	$V_{IN} = V_{OUT} + 2\text{V}$		300		mA
Load Regulation	ΔV_{OUT}	$V_{IN} = V_{OUT} + 2\text{V}, 1\text{mA} \leq I_{OUT} \leq 300\text{mA}$		37		mV
Dropout Voltage (Note 1)	V_{DIF1}	$I_{OUT} = 100\text{mA}$		180		mV
	V_{DIF2}	$I_{OUT} = 200\text{mA}$		260		mV
Supply Current	I_{SS}	$V_{IN} = V_{OUT} + 2\text{V}$		2		μA
Stand-by Current	I_{CEL}	$V_{CE} = 0\text{V}$		0		μA
Line Regulation	ΔV_{OUT}	$I_{OUT} = 30\text{mA}$ $V_{OUT} + 2\text{V} \leq V_{IN} \leq 10\text{V}$		0.2		%/V
CE "High" Voltage	V_{CEH}	Start up	1.20			V
CE "Low" Voltage	V_{CEL}	Shut down			0.8	V
Short-circuit Current	I_{SHORT}	$V_{OUT} = 0\text{V}$		200		mA
Thermal Shutdown Protection	T_{sd}	$I_{OUT} = 10\text{mA}$, $V_{IN} = V_{OUT} + 2\text{V}$		100		$^\circ\text{C}$

FUNCTIONAL DESCRIPTION

1. Input Bypass Capacitor

An input capacitor is recommended. A 10uF tantalum on the input is a suitable input bypassing for almost all applications.

2. Output Capacitor

The output capacitor is critical in maintaining regulator stability, and must meet the required conditions for both minimum amount of capacitance and ESR (Equivalent Series Resistance). The minimum output capacitance required by the HT72XX-MS is 10μF, if a tantalum capacitor is used. Any increase of the output capacitance will merely improve the loop stability and transient response. The ESR of the output capacitor should be less than 0.5Ω.

3. Load Regulation

The HT72XX-MS regulates the voltage that appears between its output and ground pins, or between its output and adjust pins. In some cases, line resistances can introduce errors to the voltage across the load. To obtain the best load regulation, a few precautions are needed. Figure 1, shows a typical application using a fixed output regulator. The R_{t1} and R_{t2} are the line resistances. It is obvious that the V_{LOAD} is less than the V_{OUT} by the sum of the voltage drops along the line resistances. In this case, the load regulation seen at the degraded from the datasheet specification. To improve this, the load should be tied directly to R_{LOAD} would be the output terminal on the positive side and directly tied to the ground terminal on the negative side.





FIGURE 1. Typical Application using Fixed Output Regulator

PACKAGE INFORMATION

SOT89



SYMBOL	mm	
	min	max
A	1.40	1.60
b1	0.35	0.50
b2	0.45	0.60
c	0.36	0.46
D	4.30	4.70
D1	1.40	1.80
E	4.00	4.40
E1	2.30	2.70
e	1.50BSC	
L	0.80	1.20

Attention

■ Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.

■ MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specification of any and all MSKSEMI Semiconductor products described or contained herein.

■ Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringement of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.