












Main technical performance	
Rated electrical load	DC 20V 3.5A
Contact resistance	≤30mΩ
Insulation resistance	≥100MΩ
Pressure resistance	AC 500V 1min
Insertion force	5-20N
Operating temperature range	-40C°~+85C°
service life	5000cycles
Salt spray test	48H
Mark "★" as the key dimension	



MATING PLUG



SCHEMATIC

D	PIN	1	HB i59	Au 0.8u"/Ni 40u"
C	CURVE PIECE	1	SUS 304	Ni 40u"
B	SPRING	1	C5191	Sn 80u"/Ni 40u"
A	HOUSING	1	PA46 BLACK	
NO.	DESCRIPTION	QTY	MATERIAL	PLATING
MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE: DC SOCKET		
DECIMALS:		PAR		
X.:±0.20		DWN		
X.X:±0.10		CHKD		
X.XX:±0.05		APVD		
ANGLES:		SCALE:1:1		
X.:±1°		UNIT:MM		
X.X':±0.5°		SIZE:A4		
CUSTOMER COPY		SHEET:1F1		
		REV:A		