

Specification Sheet

Part Number: 156-01788

Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.



MOC Clip, 12 mm Transverse, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-01788

Type T50SMVCMOC12M180

Color Black (BK)

Quantity Per carton

Product Description The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.

Short Description MOC Clip, 12 mm Transverse, Assembled to T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name

T50SMVCMOC12M180-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225

Length L (Imperial) 0.74

Length L (Metric) 18.9

Fixation Method Omega Clip

Identification Plate Position none

Bundle Diameter Min (Imperial) 0.41

Bundle Diameter Min (Metric) 10.5

Bundle Diameter Max (Imperial) 0.54

Bundle Diameter Max (Metric) 13.8

Height H (Imperial) 1.43

Height H (Metric) 36.2

Depth D (Imperial) 0.39

Depth D (Metric) 10.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

