





(For Reference Only)
Stated At Compression

NOTES:

- 1:MATERIAL
 - 1-1: YCUT-FX-EH THICKNE=0.08MM
- 2:SPECIFICATIONS
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 5.0V
 - 2-3: CONTACT RESISTANCE: 50mΩ/MAX
 - 2-4: WELDING THRUST: ≥3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
- 3:DURABILITY: 20000 CYCLES
- 4:SALT SPRAY TIME: 48H
- 5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 60-120u”
- 6:REQUIREMENTS
 - 6-1:TERMINAL TO EAT FULL TIN,NOTPEELING, WELDING OBVIOUS COLOR AND OTHED ADVERSE
 - 6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




3D View






RECOMMENDED PCB LAYOUT

TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: ANTENNA SPRING L3.40*W1.00*H2.50
DECIMALS:	ANGLES:		PAR ASP-D2516-A01
X.:±0.30	X':±2°		DWN Lucas
X.X:±0.20	X.X':±1°		CHKD Ethan
X.XX:±0.15	X.XX':±0.5°	CUSTOMER COPY	APVD Jacob
		SCALE:1:1	UNIT:MM
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A


12	13	14	15
MAPX	MODIFICATION	DATE	DRAW




Carton Size 290*330*4 K3K

Carton Size 345*345*360 K=K

Customer To Use Direction Pull Out Direction (出料方向)



The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is $165^{\circ} \sim 180^{\circ}$ And The Peeling Force Is 30~120g.



MANUFACTURE DWG			东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: ANTENNA SPRING L3.40*W1.00*H2.50	
DECIMALS:	ANGLES:	PAR	ASP-D2516-A01	
X.:±0.30	X.':±2°	DWN	Lucas	
X.X:±0.20	X.X':±1°	CHKD	Ethan	
X.XX:±0.15	X.XX':±0.5°	APVD	Jacob	
CUSTOMER COPY		SCALE:1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A